

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584173

Luminaire Tested: **HC825D010-HM82555927-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555927-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1979.9 lumens
Efficiency: N/A
Efficacy: 73.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584173

CATALOG NUMBER: HC825D010-HM82555927-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584173

CATALOG NUMBER: HC825D010-HM82555927-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46473
5°	45865
10°	44188
15°	42459
20°	41285
25°	40043
30°	35931
35°	23554
40°	13026
45°	10859
50°	9902
55°	9446
60°	8782
65°	7960
70°	7204
75°	6505
80°	5913
85°	5626



TEST NUMBER: P584173

CATALOG NUMBER: HC825D010-HM82555927-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.2	7.0
10°-20°	375.2	19.0
20°-30°	534.0	27.0
30°-40°	395.3	20.0
40°-50°	195.8	9.9
50°-60°	156.2	7.9
60°-70°	108.5	5.5
70°-80°	58.5	3.0
80°-90°	17.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.5	53.0
0°-40°	1443.7	72.9
0°-60°	1795.8	90.7
0°-90°	1979.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1979.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1507	
5°	1482	139
15°	1330	375
25°	1177	534
35°	626	395
45°	249	196
55°	176	156
65°	109	108
75°	55	58
85°	16	17
90°	0	



TEST NUMBER: P584173

CATALOG NUMBER: HC825D010-HM82555927-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1507.1
2.5°	1500.5
5°	1481.7
7.5°	1452.5
10°	1411.2
12.5°	1368.6
15°	1330.0
17.5°	1292.8
20°	1258.1
22.5°	1223.5
25°	1176.9
27.5°	1109.1
30°	1009.1
32.5°	856.1
35°	625.7
37.5°	427.4
40°	323.6
42.5°	276.9
45°	249.0
47.5°	226.3
50°	206.4
52.5°	189.1
55°	175.7
57.5°	159.8
60°	142.4
62.5°	125.2
65°	109.1
67.5°	93.2
70°	79.9
72.5°	66.6
75°	54.6
77.5°	44.0
80°	33.3
82.5°	24.0
85°	15.9
87.5°	6.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)