

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584205

Luminaire Tested: **HC825D010-HM82555935-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555935-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2158.3 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584205

CATALOG NUMBER: HC825D010-HM82555935-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584205

CATALOG NUMBER: HC825D010-HM82555935-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171734
5°	145497
10°	105565
15°	79277
20°	62549
25°	50454
30°	37391
35°	15148
40°	6388
45°	3423
50°	1540
55°	774
60°	493
65°	350
70°	289
75°	191
80°	284
85°	566



TEST NUMBER: P584205

CATALOG NUMBER: HC825D010-HM82555935-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	403.6	18.7
10°-20°	697.5	32.3
20°-30°	674.3	31.2
30°-40°	296.2	13.7
40°-50°	64.0	3.0
50°-60°	14.4	0.7
60°-70°	4.9	0.2
70°-80°	1.9	0.1
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1775.4	82.3
0°-40°	2071.5	96.0
0°-60°	2149.9	99.6
0°-90°	2158.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2158.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5569	
5°	4700	404
15°	2483	697
25°	1483	674
35°	402	296
45°	78	64
55°	14	14
65°	5	5
75°	2	2
85°	2	2
90°	0	



TEST NUMBER: P584205

CATALOG NUMBER: HC825D010-HM82555935-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5569.2
1°	5527.6
2°	5413.8
3°	5208.5
4°	4963.3
5°	4700.4
6°	4413.4
7°	4124.8
8°	3853.9
9°	3602.3
10°	3371.4
11°	3153.4
12°	2957.8
13°	2779.9
14°	2622.7
15°	2483.3
17.5°	2170.6
20°	1906.1
22.5°	1673.7
25°	1482.9
27.5°	1288.9
30°	1050.1
32.5°	713.4
35°	402.4
37.5°	237.2
40°	158.7
42.5°	112.2
45°	78.5
47.5°	51.3
50°	32.1
52.5°	19.3
55°	14.4
57.5°	11.2
60°	8.0
62.5°	6.4
65°	4.8
67.5°	3.2
70°	3.2
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6



TEST NUMBER: P584205

CATALOG NUMBER: HC825D010-HM82555935-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°		1.6
87.5°		1.6



(END OF REPORT)