

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584211

Luminaire Tested: **HC825D010-HM82555935-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555935-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2677.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584211

CATALOG NUMBER: HC825D010-HM82555935-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584211

CATALOG NUMBER: HC825D010-HM82555935-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59		
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64251
5°	62521
10°	62045
15°	61122
20°	59271
25°	57058
30°	53300
35°	44111
40°	26632
45°	17936
50°	12924
55°	7371
60°	3244
65°	1160
70°	433
75°	191
80°	0
85°	0



TEST NUMBER: P584211

CATALOG NUMBER: HC825D010-HM82555935-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	7.2
10°-20°	538.1	20.1
20°-30°	767.5	28.7
30°-40°	698.9	26.1
40°-50°	329.7	12.3
50°-60°	129.7	4.8
60°-70°	20.6	0.8
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1497.5	55.9
0°-40°	2196.4	82.0
0°-60°	2655.8	99.2
0°-90°	2677.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2677.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2084	
5°	2020	192
15°	1915	538
25°	1677	768
35°	1172	699
45°	411	330
55°	137	130
65°	16	21
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P584211

CATALOG NUMBER: HC825D010-HM82555935-81WDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	2083.6
2.5°	2056.4
5°	2019.8
7.5°	1999.1
10°	1981.5
12.5°	1952.9
15°	1914.6
17.5°	1866.7
20°	1806.2
22.5°	1742.4
25°	1677.0
27.5°	1597.3
30°	1496.9
32.5°	1361.4
35°	1171.8
37.5°	905.4
40°	661.6
42.5°	508.6
45°	411.3
47.5°	338.0
50°	269.4
52.5°	202.4
55°	137.1
57.5°	86.1
60°	52.6
62.5°	31.9
65°	15.9
67.5°	7.9
70°	4.8
72.5°	1.6
75°	1.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)