

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583791

Luminaire Tested: **HC810D010-HM80520930-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520930-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1114.1 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583791

CATALOG NUMBER: HC810D010-HM80520930-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P583791

CATALOG NUMBER: HC810D010-HM80520930-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68		
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25505
5°	24934
10°	24167
15°	23681
20°	23466
25°	23116
30°	21895
35°	18190
40°	10712
45°	7086
50°	5574
55°	4102
60°	2855
65°	1737
70°	757
75°	334
80°	249
85°	0



TEST NUMBER: P583791

CATALOG NUMBER: HC810D010-HM80520930-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.9	6.8
10°-20°	209.7	18.8
20°-30°	310.7	27.9
30°-40°	287.1	25.8
40°-50°	132.4	11.9
50°-60°	69.6	6.2
60°-70°	24.6	2.2
70°-80°	3.8	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.2	53.5
0°-40°	883.3	79.3
0°-60°	1085.2	97.4
0°-90°	1114.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1114.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	827	
5°	806	76
15°	742	210
25°	679	311
35°	483	287
45°	162	132
55°	76	70
65°	24	25
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P583791

CATALOG NUMBER: HC810D010-HM80520930-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	827.1
2.5°	820.1
5°	805.5
7.5°	789.4
10°	771.8
12.5°	755.0
15°	741.8
17.5°	729.7
20°	715.1
22.5°	699.0
25°	679.4
27.5°	652.8
30°	614.9
32.5°	561.0
35°	483.2
37.5°	371.2
40°	266.1
42.5°	199.7
45°	162.5
47.5°	138.0
50°	116.2
52.5°	95.2
55°	76.3
57.5°	60.2
60°	46.3
62.5°	35.0
65°	23.8
67.5°	14.1
70°	8.4
72.5°	4.9
75°	2.8
77.5°	2.0
80°	1.4
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)