

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583806

Luminaire Tested: **HC810D010-HM80520935-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520935-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1107.7 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583806

CATALOG NUMBER: HC810D010-HM80520935-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P583806

CATALOG NUMBER: HC810D010-HM80520935-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68				68
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62				62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47				47
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43				43
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20756
5°	20581
10°	20312
15°	20546
20°	22183
25°	24259
30°	23967
35°	19884
40°	11698
45°	7645
50°	5929
55°	3935
60°	1912
65°	598
70°	198
75°	167
80°	124
85°	248



TEST NUMBER: P583806

CATALOG NUMBER: HC810D010-HM80520935-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.0	5.7
10°-20°	184.9	16.7
20°-30°	323.2	29.2
30°-40°	314.4	28.4
40°-50°	143.0	12.9
50°-60°	66.3	6.0
60°-70°	11.1	1.0
70°-80°	1.3	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.1	51.6
0°-40°	885.5	79.9
0°-60°	1094.8	98.8
0°-90°	1107.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1107.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	673	
5°	665	63
15°	644	185
25°	713	323
35°	528	314
45°	175	143
55°	73	66
65°	8	11
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P583806

CATALOG NUMBER: HC810D010-HM80520935-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	673.1
2.5°	671.6
5°	664.9
7.5°	657.6
10°	648.7
12.5°	642.0
15°	643.6
17.5°	655.3
20°	676.0
22.5°	699.7
25°	713.0
27.5°	705.7
30°	673.1
32.5°	616.1
35°	528.2
37.5°	406.8
40°	290.6
42.5°	216.7
45°	175.3
47.5°	148.0
50°	123.6
52.5°	98.3
55°	73.2
57.5°	50.2
60°	31.0
62.5°	17.1
65°	8.2
67.5°	3.7
70°	2.2
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)