

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583798

Luminaire Tested: **HC810D010-HM80520935-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520935-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1092.2 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583798

CATALOG NUMBER: HC810D010-HM80520935-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583798

CATALOG NUMBER: HC810D010-HM80520935-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	65	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49952
5°	45518
10°	38893
15°	33916
20°	30229
25°	26818
30°	21955
35°	12607
40°	5595
45°	3253
50°	1881
55°	1075
60°	592
65°	379
70°	270
75°	167
80°	124
85°	248



TEST NUMBER: P583798

CATALOG NUMBER: HC810D010-HM80520935-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	12.2
10°-20°	298.6	27.3
20°-30°	357.5	32.7
30°-40°	216.3	19.8
40°-50°	60.6	5.5
50°-60°	18.8	1.7
60°-70°	5.4	0.5
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	789.2	72.3
0°-40°	1005.5	92.1
0°-60°	1084.9	99.3
0°-90°	1092.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1620	
5°	1470	133
15°	1062	299
25°	788	357
35°	335	216
45°	75	61
55°	20	19
65°	5	5
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P583798

CATALOG NUMBER: HC810D010-HM80520935-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1619.9
2.5°	1574.0
5°	1470.5
7.5°	1353.7
10°	1242.1
12.5°	1144.5
15°	1062.4
17.5°	990.0
20°	921.2
22.5°	857.6
25°	788.2
27.5°	709.8
30°	616.6
32.5°	496.1
35°	334.9
37.5°	208.5
40°	139.0
42.5°	99.8
45°	74.6
47.5°	54.7
50°	39.2
52.5°	27.4
55°	20.0
57.5°	13.3
60°	9.6
62.5°	6.6
65°	5.2
67.5°	3.7
70°	3.0
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)