

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583807

Luminaire Tested: **HC810D010-HM80520935-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC810D010-HM80520935-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1242.4 lumens  
Efficiency: N/A  
Efficacy: 125.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583807

CATALOG NUMBER: HC810D010-HM80520935-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583807

CATALOG NUMBER: HC810D010-HM80520935-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29806
5°	29007
10°	28785
15°	28358
20°	27496
25°	26474
30°	24729
35°	20460
40°	12354
45°	8321
50°	5997
55°	3419
60°	1505
65°	547
70°	198
75°	83
80°	0
85°	0



TEST NUMBER: P583807

CATALOG NUMBER: HC810D010-HM80520935-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.0	7.2
10°-20°	249.6	20.1
20°-30°	356.1	28.7
30°-40°	324.3	26.1
40°-50°	153.0	12.3
50°-60°	60.1	4.8
60°-70°	9.6	0.8
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.7	55.9
0°-40°	1019.0	82.0
0°-60°	1232.1	99.2
0°-90°	1242.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1242.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	967	
5°	937	89
15°	888	250
25°	778	356
35°	544	324
45°	191	153
55°	64	60
65°	8	10
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583807

CATALOG NUMBER: HC810D010-HM80520935-81WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	966.6
2.5°	954.0
5°	937.1
7.5°	927.5
10°	919.3
12.5°	905.9
15°	888.3
17.5°	866.0
20°	837.9
22.5°	808.3
25°	778.1
27.5°	741.0
30°	694.5
32.5°	631.7
35°	543.5
37.5°	420.1
40°	306.9
42.5°	236.0
45°	190.8
47.5°	156.7
50°	125.0
52.5°	93.9
55°	63.6
57.5°	39.9
60°	24.4
62.5°	14.8
65°	7.5
67.5°	3.7
70°	2.2
72.5°	0.7
75°	0.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)