

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584324

Luminaire Tested: **HC830D010-HM82555930-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555930-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2888.4 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584324

CATALOG NUMBER: HC830D010-HM82555930-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584324

CATALOG NUMBER: HC830D010-HM82555930-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229829
5°	194714
10°	141277
15°	106093
20°	83709
25°	67524
30°	50038
35°	20271
40°	8550
45°	4583
50°	2058
55°	1038
60°	660
65°	467
70°	388
75°	250
80°	373
85°	743



TEST NUMBER: P584324

CATALOG NUMBER: HC830D010-HM82555930-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	540.1	18.7
10°-20°	933.4	32.3
20°-30°	902.4	31.2
30°-40°	396.4	13.7
40°-50°	85.7	3.0
50°-60°	19.2	0.7
60°-70°	6.6	0.2
70°-80°	2.5	0.1
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2375.9	82.3
0°-40°	2772.3	96.0
0°-60°	2877.2	99.6
0°-90°	2888.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2888.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7453	
5°	6290	540
15°	3323	933
25°	1985	902
35°	538	396
45°	105	86
55°	19	19
65°	6	7
75°	2	3
85°	2	2
90°	0	



TEST NUMBER: P584324

CATALOG NUMBER: HC830D010-HM82555930-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7453.2
1°	7397.5
2°	7245.2
3°	6970.5
4°	6642.3
5°	6290.4
6°	5906.5
7°	5520.3
8°	5157.6
9°	4820.8
10°	4511.9
11°	4220.1
12°	3958.3
13°	3720.3
14°	3509.9
15°	3323.3
17.5°	2905.0
20°	2550.9
22.5°	2239.8
25°	1984.6
27.5°	1724.9
30°	1405.3
32.5°	954.8
35°	538.5
37.5°	317.6
40°	212.4
42.5°	150.2
45°	105.1
47.5°	68.6
50°	42.9
52.5°	25.8
55°	19.3
57.5°	15.0
60°	10.7
62.5°	8.6
65°	6.4
67.5°	4.3
70°	4.3
72.5°	2.1
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1



TEST NUMBER: P584324

CATALOG NUMBER: HC830D010-HM82555930-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°	2.1
87.5°	2.1



(END OF REPORT)