

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584331

Luminaire Tested: **HC830D010-HM82555930-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555930-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3394.1 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584331

CATALOG NUMBER: HC830D010-HM82555930-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584331

CATALOG NUMBER: HC830D010-HM82555930-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77701
5°	75952
10°	73621
15°	72136
20°	71488
25°	70416
30°	66706
35°	55420
40°	32638
45°	21587
50°	16992
55°	12505
60°	8684
65°	5290
70°	2308
75°	1025
80°	764
85°	0



TEST NUMBER: P584331

CATALOG NUMBER: HC830D010-HM82555930-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.1	6.8
10°-20°	638.8	18.8
20°-30°	946.4	27.9
30°-40°	874.6	25.8
40°-50°	403.2	11.9
50°-60°	212.1	6.2
60°-70°	74.9	2.2
70°-80°	11.8	0.3
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1816.3	53.5
0°-40°	2690.9	79.3
0°-60°	3306.2	97.4
0°-90°	3394.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3394.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2520	
5°	2454	231
15°	2260	639
25°	2070	946
35°	1472	875
45°	495	403
55°	233	212
65°	72	75
75°	9	12
85°	0	1
90°	0	



TEST NUMBER: P584331

CATALOG NUMBER: HC830D010-HM82555930-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2519.8
2.5°	2498.4
5°	2453.7
7.5°	2404.6
10°	2351.2
12.5°	2300.0
15°	2259.6
17.5°	2223.2
20°	2178.5
22.5°	2129.4
25°	2069.6
27.5°	1988.6
30°	1873.4
32.5°	1709.1
35°	1472.2
37.5°	1130.9
40°	810.8
42.5°	608.1
45°	495.0
47.5°	420.3
50°	354.2
52.5°	290.1
55°	232.6
57.5°	183.5
60°	140.8
62.5°	106.7
65°	72.5
67.5°	42.7
70°	25.6
72.5°	15.0
75°	8.6
77.5°	6.4
80°	4.3
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)