

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584325

Luminaire Tested: **HC830D010-HM82555930-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555930-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2856.4 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584325

CATALOG NUMBER: HC830D010-HM82555930-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584325

CATALOG NUMBER: HC830D010-HM82555930-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 98 | 98 | 96 | 95 | 95 | 93 | 92 | 90 | | | |
| 2 | 105 | 99 | 94 | 90 | 102 | 97 | 92 | 88 | 94 | 90 | 87 | 91 | 87 | 85 | 88 | 85 | 83 | 81 | | | |
| 3 | 98 | 90 | 84 | 79 | 96 | 89 | 83 | 79 | 86 | 81 | 77 | 84 | 80 | 76 | 81 | 78 | 75 | 73 | | | |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 80 | 74 | 70 | 77 | 73 | 69 | 75 | 72 | 68 | 67 | | | |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 69 | 64 | 74 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | |
| 6 | 82 | 71 | 64 | 59 | 80 | 70 | 64 | 59 | 69 | 63 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | |
| 7 | 77 | 66 | 59 | 54 | 76 | 66 | 59 | 54 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 53 | 52 | | | |
| 8 | 73 | 62 | 55 | 50 | 71 | 61 | 55 | 50 | 60 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 49 | 48 | | | |
| 9 | 69 | 58 | 51 | 47 | 68 | 57 | 51 | 47 | 56 | 51 | 46 | 55 | 50 | 46 | 55 | 50 | 46 | 45 | | | |
| 10 | 65 | 55 | 48 | 44 | 64 | 54 | 48 | 44 | 53 | 47 | 43 | 52 | 47 | 43 | 52 | 47 | 43 | 42 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 71198 |
| 5° | 71006 |
| 10° | 69826 |
| 15° | 68806 |
| 20° | 67153 |
| 25° | 63748 |
| 30° | 52580 |
| 35° | 27070 |
| 40° | 18126 |
| 45° | 15538 |
| 50° | 13408 |
| 55° | 11704 |
| 60° | 10398 |
| 65° | 9347 |
| 70° | 8466 |
| 75° | 7625 |
| 80° | 6819 |
| 85° | 6828 |



TEST NUMBER: P584325

CATALOG NUMBER: HC830D010-HM82555930-81NDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 216.9 | 7.6 |
| 10°-20° | 606.4 | 21.2 |
| 20°-30° | 840.2 | 29.4 |
| 30°-40° | 504.7 | 17.7 |
| 40°-50° | 276.2 | 9.7 |
| 50°-60° | 196.2 | 6.9 |
| 60°-70° | 127.4 | 4.5 |
| 70°-80° | 68.1 | 2.4 |
| 80°-90° | 20.4 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1663.5 | 58.2 |
| 0°-40° | 2168.1 | 75.9 |
| 0°-60° | 2640.6 | 92.4 |
| 0°-90° | 2856.4 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2856.4 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2309 | |
| 5° | 2294 | 217 |
| 15° | 2155 | 606 |
| 25° | 1874 | 840 |
| 35° | 719 | 505 |
| 45° | 356 | 276 |
| 55° | 218 | 196 |
| 65° | 128 | 127 |
| 75° | 64 | 68 |
| 85° | 19 | 20 |
| 90° | 0 | |



TEST NUMBER: P584325

CATALOG NUMBER: HC830D010-HM82555930-81NDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2308.9 |
| 2.5° | 2304.6 |
| 5° | 2293.9 |
| 7.5° | 2268.4 |
| 10° | 2230.0 |
| 12.5° | 2193.7 |
| 15° | 2155.3 |
| 17.5° | 2106.2 |
| 20° | 2046.4 |
| 22.5° | 1973.9 |
| 25° | 1873.6 |
| 27.5° | 1715.7 |
| 30° | 1476.7 |
| 32.5° | 1081.9 |
| 35° | 719.1 |
| 37.5° | 531.4 |
| 40° | 450.3 |
| 42.5° | 399.0 |
| 45° | 356.3 |
| 47.5° | 315.8 |
| 50° | 279.5 |
| 52.5° | 245.4 |
| 55° | 217.7 |
| 57.5° | 192.0 |
| 60° | 168.6 |
| 62.5° | 147.2 |
| 65° | 128.1 |
| 67.5° | 108.8 |
| 70° | 93.9 |
| 72.5° | 76.8 |
| 75° | 64.0 |
| 77.5° | 51.2 |
| 80° | 38.4 |
| 82.5° | 27.7 |
| 85° | 19.3 |
| 87.5° | 8.6 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)