

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584338

Luminaire Tested: **HC830D010-HM82555935-81MDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584338  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC830D010-HM82555935-81MDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3167.7 lumens  
Efficiency: N/A  
Efficacy: 113.1 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584338

CATALOG NUMBER: HC830D010-HM82555935-81MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584338

CATALOG NUMBER: HC830D010-HM82555935-81MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	144872
5°	132016
10°	112795
15°	98368
20°	87676
25°	77769
30°	63675
35°	36564
40°	16226
45°	9441
50°	5455
55°	3113
60°	1714
65°	1094
70°	775
75°	512
80°	373
85°	743



TEST NUMBER: P584338

CATALOG NUMBER: HC830D010-HM82555935-81MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	386.1	12.2
10°-20°	866.1	27.3
20°-30°	1036.8	32.7
30°-40°	627.2	19.8
40°-50°	175.8	5.5
50°-60°	54.6	1.7
60°-70°	15.6	0.5
70°-80°	4.2	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2289.0	72.3
0°-40°	2916.2	92.1
0°-60°	3146.5	99.3
0°-90°	3167.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3167.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4698	
5°	4265	386
15°	3081	866
25°	2286	1037
35°	971	627
45°	216	176
55°	58	55
65°	15	16
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P584338

CATALOG NUMBER: HC830D010-HM82555935-81MDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4698.1
2.5°	4565.2
5°	4264.9
7.5°	3926.2
10°	3602.3
12.5°	3319.3
15°	3081.3
17.5°	2871.2
20°	2671.8
22.5°	2487.4
25°	2285.7
27.5°	2058.5
30°	1788.3
32.5°	1438.8
35°	971.3
37.5°	604.7
40°	403.1
42.5°	289.5
45°	216.5
47.5°	158.7
50°	113.7
52.5°	79.3
55°	57.9
57.5°	38.6
60°	27.8
62.5°	19.3
65°	15.0
67.5°	10.7
70°	8.6
72.5°	4.3
75°	4.3
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)