

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583888

Luminaire Tested: **HC815D010-HM80520840-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583888  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC815D010-HM80520840-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1767.0 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583888

CATALOG NUMBER: HC815D010-HM80520840-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583888

CATALOG NUMBER: HC815D010-HM80520840-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     | 0   |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 |    |
| 1   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 101 | 99  | 97  | 98  | 96  | 94  | 94  | 93  | 91  | 89  | 89  |    |
| 2   | 104 | 98  | 92  | 88  | 102 | 96  | 91  | 87  | 92  | 88  | 85  | 89  | 86  | 83  | 86  | 84  | 81  | 79  | 79  |    |
| 3   | 97  | 89  | 83  | 77  | 95  | 87  | 82  | 77  | 85  | 80  | 76  | 82  | 78  | 74  | 80  | 76  | 73  | 71  | 71  |    |
| 4   | 91  | 81  | 74  | 69  | 89  | 80  | 74  | 69  | 78  | 72  | 68  | 76  | 71  | 67  | 74  | 70  | 66  | 64  | 64  |    |
| 5   | 85  | 75  | 68  | 62  | 83  | 74  | 67  | 62  | 72  | 66  | 61  | 70  | 65  | 61  | 68  | 64  | 60  | 58  | 58  |    |
| 6   | 80  | 69  | 62  | 57  | 78  | 68  | 61  | 56  | 67  | 61  | 56  | 65  | 60  | 56  | 64  | 59  | 55  | 53  | 53  |    |
| 7   | 75  | 64  | 57  | 52  | 74  | 63  | 57  | 52  | 62  | 56  | 51  | 61  | 55  | 51  | 60  | 55  | 51  | 49  | 49  |    |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 45  | 45  |    |
| 9   | 67  | 56  | 49  | 44  | 66  | 55  | 49  | 44  | 54  | 48  | 44  | 53  | 48  | 44  | 52  | 47  | 44  | 42  | 42  |    |
| 10  | 64  | 52  | 46  | 41  | 62  | 52  | 45  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 49  | 44  | 41  | 39  | 39  |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 41478 |
| 5°  | 40940 |
| 10° | 39441 |
| 15° | 37894 |
| 20° | 36848 |
| 25° | 35739 |
| 30° | 32071 |
| 35° | 21024 |
| 40° | 11621 |
| 45° | 9690  |
| 50° | 8837  |
| 55° | 8435  |
| 60° | 7839  |
| 65° | 7114  |
| 70° | 6428  |
| 75° | 5802  |
| 80° | 5292  |
| 85° | 5024  |



TEST NUMBER: P583888

CATALOG NUMBER: HC815D010-HM80520840-81PSMDW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 124.3  | 7.0       |
| 10°-20°   | 334.9  | 19.0      |
| 20°-30°   | 476.6  | 27.0      |
| 30°-40°   | 352.8  | 20.0      |
| 40°-50°   | 174.7  | 9.9       |
| 50°-60°   | 139.5  | 7.9       |
| 60°-70°   | 96.8   | 5.5       |
| 70°-80°   | 52.2   | 3.0       |
| 80°-90°   | 15.3   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 935.8  | 53.0      |
| 0°-40°    | 1288.6 | 72.9      |
| 0°-60°    | 1602.7 | 90.7      |
| 0°-90°    | 1767.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1767.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1345 |      |
| 5°  | 1323 | 124  |
| 15° | 1187 | 335  |
| 25° | 1050 | 477  |
| 35° | 558  | 353  |
| 45° | 222  | 175  |
| 55° | 157  | 139  |
| 65° | 98   | 97   |
| 75° | 49   | 52   |
| 85° | 14   | 15   |
| 90° | 0    |      |



TEST NUMBER: P583888

CATALOG NUMBER: HC815D010-HM80520840-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1345.1 |
| 2.5°  | 1339.2 |
| 5°    | 1322.6 |
| 7.5°  | 1296.5 |
| 10°   | 1259.6 |
| 12.5° | 1221.5 |
| 15°   | 1187.0 |
| 17.5° | 1153.8 |
| 20°   | 1122.9 |
| 22.5° | 1092.1 |
| 25°   | 1050.4 |
| 27.5° | 989.9  |
| 30°   | 900.7  |
| 32.5° | 764.1  |
| 35°   | 558.5  |
| 37.5° | 381.4  |
| 40°   | 288.7  |
| 42.5° | 247.1  |
| 45°   | 222.2  |
| 47.5° | 202.0  |
| 50°   | 184.2  |
| 52.5° | 168.7  |
| 55°   | 156.9  |
| 57.5° | 142.6  |
| 60°   | 127.1  |
| 62.5° | 111.7  |
| 65°   | 97.5   |
| 67.5° | 83.1   |
| 70°   | 71.3   |
| 72.5° | 59.4   |
| 75°   | 48.7   |
| 77.5° | 39.2   |
| 80°   | 29.8   |
| 82.5° | 21.4   |
| 85°   | 14.2   |
| 87.5° | 5.9    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)