

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584380

Luminaire Tested: **HC835D010-HM82555827-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555827-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3999.8 lumens
Efficiency: N/A
Efficacy: 118.7 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584380

CATALOG NUMBER: HC835D010-HM82555827-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584380

CATALOG NUMBER: HC835D010-HM82555827-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74941
5°	74318
10°	73339
15°	74176
20°	80102
25°	87595
30°	86535
35°	71784
40°	42251
45°	27600
50°	21396
55°	14215
60°	6914
65°	2145
70°	721
75°	643
80°	462
85°	920



TEST NUMBER: P584380

CATALOG NUMBER: HC835D010-HM82555827-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.4	5.7
10°-20°	667.5	16.7
20°-30°	1167.1	29.2
30°-40°	1135.3	28.4
40°-50°	516.3	12.9
50°-60°	239.4	6.0
60°-70°	40.1	1.0
70°-80°	4.9	0.1
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2062.0	51.6
0°-40°	3197.3	79.9
0°-60°	3953.0	98.8
0°-90°	3999.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3999.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2430	
5°	2401	227
15°	2324	668
25°	2574	1167
35°	1907	1135
45°	633	516
55°	264	239
65°	29	40
75°	5	5
85°	3	2
90°	0	



TEST NUMBER: P584380

CATALOG NUMBER: HC835D010-HM82555827-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2430.3
2.5°	2425.0
5°	2400.9
7.5°	2374.2
10°	2342.2
12.5°	2318.1
15°	2323.5
17.5°	2366.2
20°	2441.0
22.5°	2526.5
25°	2574.5
27.5°	2547.8
30°	2430.3
32.5°	2224.7
35°	1906.9
37.5°	1468.9
40°	1049.6
42.5°	782.5
45°	632.9
47.5°	534.2
50°	446.0
52.5°	355.2
55°	264.4
57.5°	181.6
60°	112.1
62.5°	61.5
65°	29.4
67.5°	13.3
70°	8.0
72.5°	5.4
75°	5.4
77.5°	2.6
80°	2.6
82.5°	2.6
85°	2.6
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)