

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584382

Luminaire Tested: **HC835D010-HM82555827-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555827-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4248.1 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584382

CATALOG NUMBER: HC835D010-HM82555827-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584382

CATALOG NUMBER: HC835D010-HM82555827-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97258
5°	95066
10°	92151
15°	90285
20°	89474
25°	88136
30°	83487
35°	69363
40°	40850
45°	27020
50°	21266
55°	15650
60°	10867
65°	6625
70°	2894
75°	1275
80°	959
85°	0



TEST NUMBER: P584382

CATALOG NUMBER: HC835D010-HM82555827-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.2	6.8
10°-20°	799.5	18.8
20°-30°	1184.6	27.9
30°-40°	1094.6	25.8
40°-50°	504.7	11.9
50°-60°	265.5	6.2
60°-70°	93.8	2.2
70°-80°	14.8	0.3
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2273.3	53.5
0°-40°	3367.9	79.3
0°-60°	4138.1	97.4
0°-90°	4248.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4248.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3154	
5°	3071	289
15°	2828	800
25°	2590	1185
35°	1843	1095
45°	620	505
55°	291	265
65°	91	94
75°	11	15
85°	0	1
90°	0	



TEST NUMBER: P584382

CATALOG NUMBER: HC835D010-HM82555827-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3154.0
2.5°	3127.3
5°	3071.2
7.5°	3009.7
10°	2943.0
12.5°	2878.9
15°	2828.1
17.5°	2782.7
20°	2726.6
22.5°	2665.2
25°	2590.4
27.5°	2489.0
30°	2344.7
32.5°	2139.1
35°	1842.6
37.5°	1415.4
40°	1014.8
42.5°	761.1
45°	619.6
47.5°	526.2
50°	443.3
52.5°	363.2
55°	291.1
57.5°	229.7
60°	176.2
62.5°	133.6
65°	90.8
67.5°	53.4
70°	32.1
72.5°	18.7
75°	10.7
77.5°	8.0
80°	5.4
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)