

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584392

Luminaire Tested: **HC835D010-HM82555830-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555830-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3530.4 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584392

CATALOG NUMBER: HC835D010-HM82555830-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584392

CATALOG NUMBER: HC835D010-HM82555830-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280913
5°	237991
10°	172673
15°	129673
20°	102315
25°	82529
30°	61158
35°	24777
40°	10450
45°	5604
50°	2519
55°	1269
60°	808
65°	576
70°	478
75°	310
80°	462
85°	920



TEST NUMBER: P584392

CATALOG NUMBER: HC835D010-HM82555830-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	660.1	18.7
10°-20°	1140.8	32.3
20°-30°	1103.0	31.2
30°-40°	484.5	13.7
40°-50°	104.7	3.0
50°-60°	23.5	0.7
60°-70°	8.1	0.2
70°-80°	3.1	0.1
80°-90°	2.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2904.0	82.3
0°-40°	3388.5	96.0
0°-60°	3516.7	99.6
0°-90°	3530.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3530.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9110	
5°	7688	660
15°	4062	1141
25°	2426	1103
35°	658	484
45°	128	105
55°	24	24
65°	8	8
75°	3	3
85°	3	2
90°	0	



TEST NUMBER: P584392

CATALOG NUMBER: HC835D010-HM82555830-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9109.8
1°	9041.7
2°	8855.5
3°	8519.8
4°	8118.6
5°	7688.5
6°	7219.1
7°	6747.1
8°	6304.0
9°	5892.2
10°	5514.6
11°	5158.1
12°	4838.1
13°	4547.0
14°	4290.0
15°	4061.9
17.5°	3550.6
20°	3117.9
22.5°	2737.7
25°	2425.6
27.5°	2108.4
30°	1717.6
32.5°	1167.0
35°	658.2
37.5°	388.2
40°	259.6
42.5°	183.5
45°	128.5
47.5°	83.9
50°	52.5
52.5°	31.5
55°	23.6
57.5°	18.3
60°	13.1
62.5°	10.5
65°	7.9
67.5°	5.3
70°	5.3
72.5°	2.6
75°	2.6
77.5°	2.6
80°	2.6
82.5°	2.6



TEST NUMBER: P584392

CATALOG NUMBER: HC835D010-HM82555830-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°	2.6
87.5°	2.6



(END OF REPORT)