

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593561

Luminaire Tested: **HC815D010-HM80520850-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520850-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1825.3 lumens
Efficiency: N/A
Efficacy: 130.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593561

CATALOG NUMBER: HC815D010-HM80520850-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593561

CATALOG NUMBER: HC815D010-HM80520850-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36492
5°	36448
10°	36090
15°	35656
20°	35322
25°	34926
30°	32958
35°	26837
40°	14830
45°	9895
50°	8774
55°	8242
60°	8135
65°	8063
70°	7294
75°	6517
80°	5700
85°	5024



TEST NUMBER: P593561

CATALOG NUMBER: HC815D010-HM80520850-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.6	6.1
10°-20°	315.4	17.3
20°-30°	468.6	25.7
30°-40°	422.0	23.1
40°-50°	187.1	10.2
50°-60°	138.5	7.6
60°-70°	107.8	5.9
70°-80°	58.4	3.2
80°-90°	16.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	895.5	49.1
0°-40°	1317.5	72.2
0°-60°	1643.1	90.0
0°-90°	1825.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1825.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1183	
5°	1178	112
15°	1117	315
25°	1026	469
35°	713	422
45°	227	187
55°	153	139
65°	110	108
75°	55	58
85°	14	16
90°	0	



TEST NUMBER: P593561

CATALOG NUMBER: HC815D010-HM80520850-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1183.4
2.5°	1181.0
5°	1177.5
7.5°	1168.0
10°	1152.6
12.5°	1134.7
15°	1116.9
17.5°	1099.1
20°	1076.4
22.5°	1053.9
25°	1026.5
27.5°	985.0
30°	925.6
32.5°	840.0
35°	712.9
37.5°	532.2
40°	368.4
42.5°	272.1
45°	226.9
47.5°	200.8
50°	182.9
52.5°	166.3
55°	153.3
57.5°	142.6
60°	131.9
62.5°	122.4
65°	110.5
67.5°	96.3
70°	80.9
72.5°	67.7
75°	54.7
77.5°	42.8
80°	32.1
82.5°	22.5
85°	14.2
87.5°	5.9
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)