

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583902

Luminaire Tested: **HC815D010-HM80520927-81NDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583902  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC815D010-HM80520927-81NDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1288.8 lumens  
Efficiency: N/A  
Efficacy: 92.1 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583902

CATALOG NUMBER: HC815D010-HM80520927-81NDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583902

CATALOG NUMBER: HC815D010-HM80520927-81NDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	242599
5°	155606
10°	70292
15°	42414
20°	32323
25°	26100
30°	19128
35°	6927
40°	2584
45°	1173
50°	374
55°	91
60°	49
65°	58
70°	0
75°	0
80°	142
85°	283



TEST NUMBER: P583902

CATALOG NUMBER: HC815D010-HM80520927-81NDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	383.4	29.7
10°-20°	389.4	30.2
20°-30°	348.6	27.0
30°-40°	140.4	10.9
40°-50°	23.0	1.8
50°-60°	2.1	0.2
60°-70°	0.7	0.1
70°-80°	0.5	0.0
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.4	87.0
0°-40°	1261.9	97.9
0°-60°	1287.0	99.9
0°-90°	1289.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1288.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7867	
5°	5027	383
15°	1329	389
25°	767	349
35°	184	140
45°	27	23
55°	2	2
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P583902

CATALOG NUMBER: HC815D010-HM80520927-81NDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7867.3
0.5°	7843.0
1°	7741.5
1.5°	7578.4
2°	7331.0
2.5°	7038.5
3°	6672.3
3.5°	6270.6
4°	5873.2
4.5°	5427.9
5°	5027.0
5.5°	4590.6
6°	4236.5
6.5°	3867.7
7°	3577.9
7.5°	3271.6
8°	3025.0
8.5°	2777.8
9°	2592.1
9.5°	2387.2
10°	2244.9
12.5°	1655.7
15°	1328.6
17.5°	1135.1
20°	985.0
22.5°	865.2
25°	767.1
27.5°	669.0
30°	537.2
32.5°	345.4
35°	184.0
37.5°	101.6
40°	64.2
42.5°	42.5
45°	26.9
47.5°	16.5
50°	7.8
52.5°	2.7
55°	1.7
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8



TEST NUMBER: P583902

CATALOG NUMBER: HC815D010-HM80520927-81NDC

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







67.5°		0.8
70°		0.0



(END OF REPORT)