

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584418

Luminaire Tested: **HC835D010-HM82555835-81WDWB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584418  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC835D010-HM82555835-81WDWB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4552.1 lumens  
Efficiency: N/A  
Efficacy: 135.1 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584418

CATALOG NUMBER: HC835D010-HM82555835-81WDWB

### Luminous Intensity Polar Plot





TEST NUMBER: P584418

CATALOG NUMBER: HC835D010-HM82555835-81WDWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	79946
5°	79394
10°	79188
15°	81266
20°	87978
25°	94325
30°	92214
35°	76787
40°	47174
45°	32663
50°	24927
55°	16349
60°	10225
65°	7669
70°	7727
75°	8888
80°	9802
85°	8810



TEST NUMBER: P584418

CATALOG NUMBER: HC835D010-HM82555835-81WDWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	243.7	5.4
10°-20°	730.7	16.1
20°-30°	1258.0	27.6
30°-40°	1218.8	26.8
40°-50°	600.3	13.2
50°-60°	283.3	6.2
60°-70°	111.6	2.5
70°-80°	77.0	1.7
80°-90°	28.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2232.5	49.0
0°-40°	3451.3	75.8
0°-60°	4334.9	95.2
0°-90°	4552.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4552.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2593	
5°	2565	244
15°	2546	731
25°	2772	1258
35°	2040	1219
45°	749	600
55°	304	283
65°	105	112
75°	75	77
85°	25	29
90°	0	



TEST NUMBER: P584418

CATALOG NUMBER: HC835D010-HM82555835-81WDWB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2592.6
2.5°	2584.3
5°	2564.9
7.5°	2545.6
10°	2529.0
12.5°	2526.2
15°	2545.6
17.5°	2603.6
20°	2681.0
22.5°	2750.1
25°	2772.3
27.5°	2722.5
30°	2589.8
32.5°	2371.4
35°	2039.8
37.5°	1583.8
40°	1171.9
42.5°	909.3
45°	749.0
47.5°	630.1
50°	519.6
52.5°	409.1
55°	304.1
57.5°	221.2
60°	165.8
62.5°	129.9
65°	105.1
67.5°	91.2
70°	85.7
72.5°	80.1
75°	74.6
77.5°	66.4
80°	55.2
82.5°	41.5
85°	24.9
87.5°	11.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)