

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584435

Luminaire Tested: **HC835D010-HM82555840-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555840-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4930.3 lumens
Efficiency: N/A
Efficacy: 146.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584435

CATALOG NUMBER: HC835D010-HM82555840-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584435

CATALOG NUMBER: HC835D010-HM82555840-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86585
5°	85991
10°	85767
15°	88018
20°	95286
25°	102157
30°	99873
35°	83164
40°	51094
45°	35380
50°	26999
55°	17704
60°	11076
65°	8303
70°	8367
75°	9639
80°	10637
85°	9553



TEST NUMBER: P584435

CATALOG NUMBER: HC835D010-HM82555840-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.0	5.4
10°-20°	791.5	16.1
20°-30°	1362.5	27.6
30°-40°	1320.0	26.8
40°-50°	650.2	13.2
50°-60°	306.8	6.2
60°-70°	120.9	2.5
70°-80°	83.5	1.7
80°-90°	31.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2417.9	49.0
0°-40°	3737.9	75.8
0°-60°	4695.0	95.2
0°-90°	4930.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4930.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2808	
5°	2778	264
15°	2757	791
25°	3002	1362
35°	2209	1320
45°	811	650
55°	329	307
65°	114	121
75°	81	83
85°	27	31
90°	0	



TEST NUMBER: P584435

CATALOG NUMBER: HC835D010-HM82555840-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2807.9
2.5°	2798.9
5°	2778.0
7.5°	2757.1
10°	2739.1
12.5°	2736.1
15°	2757.1
17.5°	2819.9
20°	2903.7
22.5°	2978.6
25°	3002.5
27.5°	2948.6
30°	2804.9
32.5°	2568.4
35°	2209.2
37.5°	1715.3
40°	1269.3
42.5°	984.9
45°	811.3
47.5°	682.5
50°	562.8
52.5°	443.0
55°	329.3
57.5°	239.5
60°	179.6
62.5°	140.6
65°	113.8
67.5°	98.8
70°	92.8
72.5°	86.9
75°	80.9
77.5°	71.9
80°	59.9
82.5°	44.9
85°	27.0
87.5°	12.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)