

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583922

Luminaire Tested: **HC815D010-HM80520930-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520930-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1429.3 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583922

CATALOG NUMBER: HC815D010-HM80520930-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583922

CATALOG NUMBER: HC815D010-HM80520930-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79	79	79	79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64	64	64	64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49	49	49	49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45	45	45	45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33550
5°	33115
10°	31901
15°	30657
20°	29806
25°	28907
30°	25939
35°	17008
40°	9399
45°	7841
50°	7143
55°	6822
60°	6340
65°	5750
70°	5202
75°	4694
80°	4262
85°	4104



TEST NUMBER: P583922

CATALOG NUMBER: HC815D010-HM80520930-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	7.0
10°-20°	270.9	19.0
20°-30°	385.5	27.0
30°-40°	285.3	20.0
40°-50°	141.3	9.9
50°-60°	112.8	7.9
60°-70°	78.3	5.5
70°-80°	42.2	3.0
80°-90°	12.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.9	53.0
0°-40°	1042.3	72.9
0°-60°	1296.4	90.7
0°-90°	1429.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1429.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1088	
5°	1070	101
15°	960	271
25°	850	386
35°	452	285
45°	180	141
55°	127	113
65°	79	78
75°	39	42
85°	12	12
90°	0	



TEST NUMBER: P583922

CATALOG NUMBER: HC815D010-HM80520930-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1088.0
2.5°	1083.3
5°	1069.8
7.5°	1048.6
10°	1018.8
12.5°	988.1
15°	960.3
17.5°	933.3
20°	908.3
22.5°	883.3
25°	849.6
27.5°	800.6
30°	728.5
32.5°	618.0
35°	451.8
37.5°	308.5
40°	233.5
42.5°	199.9
45°	179.8
47.5°	163.4
50°	148.9
52.5°	136.5
55°	126.9
57.5°	115.3
60°	102.8
62.5°	90.4
65°	78.8
67.5°	67.2
70°	57.7
72.5°	48.1
75°	39.4
77.5°	31.7
80°	24.0
82.5°	17.4
85°	11.6
87.5°	4.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)