

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583939

Luminaire Tested: **HC815D010-HM80520935-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583939  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC815D010-HM80520935-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1509.5 lumens  
Efficiency: N/A  
Efficacy: 107.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583939

CATALOG NUMBER: HC815D010-HM80520935-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583939

CATALOG NUMBER: HC815D010-HM80520935-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	35434
5°	34972
10°	33689
15°	32371
20°	31476
25°	30533
30°	27396
35°	17960
40°	9931
45°	8277
50°	7551
55°	7204
60°	6698
65°	6078
70°	5491
75°	4956
80°	4511
85°	4316



TEST NUMBER: P583939

CATALOG NUMBER: HC815D010-HM80520935-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.1	7.0
10°-20°	286.1	19.0
20°-30°	407.2	27.0
30°-40°	301.3	20.0
40°-50°	149.3	9.9
50°-60°	119.1	7.9
60°-70°	82.7	5.5
70°-80°	44.5	3.0
80°-90°	13.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.4	53.0
0°-40°	1100.7	72.9
0°-60°	1369.1	90.7
0°-90°	1509.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1509.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1149	
5°	1130	106
15°	1014	286
25°	897	407
35°	477	301
45°	190	149
55°	134	119
65°	83	83
75°	42	45
85°	12	13
90°	0	



TEST NUMBER: P583939

CATALOG NUMBER: HC815D010-HM80520935-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1149.1
2.5°	1144.0
5°	1129.8
7.5°	1107.4
10°	1075.9
12.5°	1043.5
15°	1014.0
17.5°	985.6
20°	959.2
22.5°	932.8
25°	897.4
27.5°	845.5
30°	769.4
32.5°	652.6
35°	477.1
37.5°	325.8
40°	246.7
42.5°	211.1
45°	189.8
47.5°	172.6
50°	157.4
52.5°	144.1
55°	134.0
57.5°	121.8
60°	108.6
62.5°	95.4
65°	83.3
67.5°	71.1
70°	60.9
72.5°	50.7
75°	41.6
77.5°	33.5
80°	25.4
82.5°	18.3
85°	12.2
87.5°	5.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)