

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583989

Luminaire Tested: **HC820D010-HM80520830-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583989
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC820D010-HM80520830-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1938.7 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583989

CATALOG NUMBER: HC820D010-HM80520830-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P583989

CATALOG NUMBER: HC820D010-HM80520830-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48324
5°	48196
10°	47394
15°	46699
20°	45580
25°	43268
30°	35685
35°	18370
40°	12298
45°	10545
50°	9100
55°	7946
60°	7055
65°	6341
70°	5743
75°	5183
80°	4635
85°	4599



TEST NUMBER: P583989

CATALOG NUMBER: HC820D010-HM80520830-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	7.6
10°-20°	411.6	21.2
20°-30°	570.3	29.4
30°-40°	342.5	17.7
40°-50°	187.5	9.7
50°-60°	133.2	6.9
60°-70°	86.5	4.5
70°-80°	46.2	2.4
80°-90°	13.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1129.1	58.2
0°-40°	1471.5	75.9
0°-60°	1792.2	92.4
0°-90°	1938.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1938.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1567	
5°	1557	147
15°	1463	412
25°	1272	570
35°	488	342
45°	242	187
55°	148	133
65°	87	86
75°	44	46
85°	13	14
90°	0	



TEST NUMBER: P583989

CATALOG NUMBER: HC820D010-HM80520830-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1567.1
2.5°	1564.3
5°	1557.0
7.5°	1539.7
10°	1513.6
12.5°	1489.0
15°	1462.8
17.5°	1429.5
20°	1389.0
22.5°	1339.8
25°	1271.7
27.5°	1164.5
30°	1002.2
32.5°	734.4
35°	488.0
37.5°	360.6
40°	305.5
42.5°	270.8
45°	241.8
47.5°	214.4
50°	189.7
52.5°	166.5
55°	147.8
57.5°	130.4
60°	114.4
62.5°	99.9
65°	86.9
67.5°	73.9
70°	63.7
72.5°	52.1
75°	43.5
77.5°	34.8
80°	26.1
82.5°	18.8
85°	13.0
87.5°	5.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)