

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584483

Luminaire Tested: **HC835D010-HM82555935-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555935-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4330.2 lumens
Efficiency: N/A
Efficacy: 128.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584483

CATALOG NUMBER: HC835D010-HM82555935-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P584483

CATALOG NUMBER: HC835D010-HM82555935-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103888
5°	101096
10°	100327
15°	98834
20°	95837
25°	92267
30°	86182
35°	71321
40°	43060
45°	29000
50°	20897
55°	11914
60°	5248
65°	1882
70°	703
75°	310
80°	0
85°	0



TEST NUMBER: P584483

CATALOG NUMBER: HC835D010-HM82555935-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.3	7.2
10°-20°	870.0	20.1
20°-30°	1241.1	28.7
30°-40°	1130.2	26.1
40°-50°	533.1	12.3
50°-60°	209.6	4.8
60°-70°	33.4	0.8
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2421.4	55.9
0°-40°	3551.6	82.0
0°-60°	4294.4	99.2
0°-90°	4330.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4330.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3369	
5°	3266	310
15°	3096	870
25°	2712	1241
35°	1895	1130
45°	665	533
55°	222	210
65°	26	33
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P584483

CATALOG NUMBER: HC835D010-HM82555935-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3369.0
2.5°	3325.3
5°	3266.0
7.5°	3232.4
10°	3204.1
12.5°	3157.7
15°	3095.9
17.5°	3018.5
20°	2920.5
22.5°	2817.5
25°	2711.8
27.5°	2582.9
30°	2420.4
32.5°	2201.3
35°	1894.6
37.5°	1464.2
40°	1069.7
42.5°	822.3
45°	665.0
47.5°	546.5
50°	435.6
52.5°	327.4
55°	221.6
57.5°	139.2
60°	85.1
62.5°	51.5
65°	25.8
67.5°	12.9
70°	7.8
72.5°	2.6
75°	2.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)