

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584503

Luminaire Tested: **HC835D010-HM82555940-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555940-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4692.4 lumens
Efficiency: N/A
Efficacy: 139.2 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584503

CATALOG NUMBER: HC835D010-HM82555940-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P584503

CATALOG NUMBER: HC835D010-HM82555940-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82410
5°	81843
10°	81630
15°	83769
20°	90692
25°	97231
30°	95056
35°	79151
40°	48631
45°	33671
50°	25694
55°	16849
60°	10546
65°	7902
70°	7961
75°	9162
80°	10122
85°	9057



TEST NUMBER: P584503

CATALOG NUMBER: HC835D010-HM82555940-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.2	5.4
10°-20°	753.3	16.1
20°-30°	1296.8	27.6
30°-40°	1256.3	26.8
40°-50°	618.8	13.2
50°-60°	292.0	6.2
60°-70°	115.1	2.5
70°-80°	79.4	1.7
80°-90°	29.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2301.2	49.0
0°-40°	3557.6	75.8
0°-60°	4468.4	95.2
0°-90°	4692.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4692.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2672	
5°	2644	251
15°	2624	753
25°	2858	1297
35°	2103	1256
45°	772	619
55°	313	292
65°	108	115
75°	77	79
85°	26	29
90°	0	



TEST NUMBER: P584503

CATALOG NUMBER: HC835D010-HM82555940-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2672.5
2.5°	2663.9
5°	2644.0
7.5°	2624.0
10°	2607.0
12.5°	2604.1
15°	2624.0
17.5°	2683.9
20°	2763.7
22.5°	2834.8
25°	2857.7
27.5°	2806.3
30°	2669.6
32.5°	2444.5
35°	2102.6
37.5°	1632.5
40°	1208.1
42.5°	937.3
45°	772.1
47.5°	649.6
50°	535.6
52.5°	421.7
55°	313.4
57.5°	228.0
60°	171.0
62.5°	133.9
65°	108.3
67.5°	94.0
70°	88.3
72.5°	82.7
75°	76.9
77.5°	68.4
80°	57.0
82.5°	42.8
85°	25.6
87.5°	11.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)