

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593714

Luminaire Tested: **HC835D010-HM82555950-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555950-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4376.1 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593714

CATALOG NUMBER: HC835D010-HM82555950-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P593714

CATALOG NUMBER: HC835D010-HM82555950-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 111 | 108 | 104 | 101 | 109 | 105 | 102 | 100 | 101 | 99 | 96 | 97 | 95 | 94 | 94 | 92 | 91 | 89 | | | |
| 2 | 104 | 97 | 92 | 87 | 101 | 95 | 90 | 86 | 92 | 88 | 84 | 89 | 85 | 82 | 86 | 83 | 81 | 79 | | | |
| 3 | 97 | 88 | 82 | 76 | 94 | 87 | 81 | 76 | 84 | 79 | 75 | 81 | 77 | 73 | 79 | 75 | 72 | 70 | | | |
| 4 | 90 | 80 | 73 | 68 | 88 | 79 | 73 | 67 | 77 | 71 | 67 | 75 | 70 | 66 | 73 | 68 | 65 | 63 | | | |
| 5 | 84 | 74 | 66 | 61 | 82 | 73 | 66 | 61 | 71 | 65 | 60 | 69 | 64 | 59 | 67 | 63 | 59 | 57 | | | |
| 6 | 79 | 68 | 61 | 55 | 77 | 67 | 60 | 55 | 65 | 59 | 55 | 64 | 58 | 54 | 62 | 58 | 54 | 52 | | | |
| 7 | 74 | 63 | 56 | 50 | 73 | 62 | 55 | 50 | 61 | 54 | 50 | 59 | 54 | 50 | 58 | 53 | 49 | 48 | | | |
| 8 | 70 | 58 | 51 | 46 | 69 | 58 | 51 | 46 | 57 | 50 | 46 | 55 | 50 | 46 | 54 | 49 | 45 | 44 | | | |
| 9 | 66 | 54 | 47 | 43 | 65 | 54 | 47 | 42 | 53 | 47 | 42 | 52 | 46 | 42 | 51 | 46 | 42 | 40 | | | |
| 10 | 62 | 51 | 44 | 39 | 61 | 50 | 44 | 39 | 49 | 43 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 37 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 87489 |
| 5° | 87383 |
| 10° | 86518 |
| 15° | 85480 |
| 20° | 84693 |
| 25° | 83740 |
| 30° | 79015 |
| 35° | 64341 |
| 40° | 35544 |
| 45° | 23728 |
| 50° | 21046 |
| 55° | 19752 |
| 60° | 19501 |
| 65° | 19328 |
| 70° | 17464 |
| 75° | 15620 |
| 80° | 13656 |
| 85° | 12065 |



TEST NUMBER: P593714

CATALOG NUMBER: HC835D010-HM82555950-81WDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 267.5 | 6.1 |
| 10°-20° | 756.1 | 17.3 |
| 20°-30° | 1123.4 | 25.7 |
| 30°-40° | 1011.7 | 23.1 |
| 40°-50° | 448.5 | 10.2 |
| 50°-60° | 332.1 | 7.6 |
| 60°-70° | 258.3 | 5.9 |
| 70°-80° | 140.0 | 3.2 |
| 80°-90° | 38.3 | 0.9 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2147.0 | 49.1 |
| 0°-40° | 3158.8 | 72.2 |
| 0°-60° | 3939.4 | 90.0 |
| 0°-90° | 4376.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4376.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2837 | |
| 5° | 2823 | 268 |
| 15° | 2678 | 756 |
| 25° | 2461 | 1123 |
| 35° | 1709 | 1012 |
| 45° | 544 | 449 |
| 55° | 367 | 332 |
| 65° | 265 | 258 |
| 75° | 131 | 140 |
| 85° | 34 | 38 |
| 90° | 0 | |



TEST NUMBER: P593714

CATALOG NUMBER: HC835D010-HM82555950-81WDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 2837.2 |
| 2.5° | 2831.5 |
| 5° | 2823.0 |
| 7.5° | 2800.1 |
| 10° | 2763.1 |
| 12.5° | 2720.4 |
| 15° | 2677.6 |
| 17.5° | 2634.9 |
| 20° | 2580.9 |
| 22.5° | 2526.7 |
| 25° | 2461.2 |
| 27.5° | 2361.5 |
| 30° | 2219.1 |
| 32.5° | 2014.0 |
| 35° | 1709.2 |
| 37.5° | 1276.1 |
| 40° | 883.0 |
| 42.5° | 652.3 |
| 45° | 544.1 |
| 47.5° | 481.4 |
| 50° | 438.7 |
| 52.5° | 398.8 |
| 55° | 367.4 |
| 57.5° | 341.8 |
| 60° | 316.2 |
| 62.5° | 293.4 |
| 65° | 264.9 |
| 67.5° | 230.7 |
| 70° | 193.7 |
| 72.5° | 162.3 |
| 75° | 131.1 |
| 77.5° | 102.5 |
| 80° | 76.9 |
| 82.5° | 54.1 |
| 85° | 34.1 |
| 87.5° | 14.3 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)