

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584053

Luminaire Tested: **HC820D010-HM80520930-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC820D010-HM80520930-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1752.7 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584053

CATALOG NUMBER: HC820D010-HM80520930-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584053

CATALOG NUMBER: HC820D010-HM80520930-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43692
5°	43571
10°	42847
15°	42220
20°	41209
25°	39118
30°	32263
35°	16609
40°	11126
45°	9537
50°	8227
55°	7183
60°	6377
65°	5735
70°	5193
75°	4670
80°	4173
85°	4175



TEST NUMBER: P584053

CATALOG NUMBER: HC820D010-HM80520930-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.1	7.6
10°-20°	372.1	21.2
20°-30°	515.6	29.4
30°-40°	309.7	17.7
40°-50°	169.5	9.7
50°-60°	120.4	6.9
60°-70°	78.2	4.5
70°-80°	41.8	2.4
80°-90°	12.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1020.7	58.2
0°-40°	1330.4	75.9
0°-60°	1620.4	92.4
0°-90°	1752.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1752.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1417	
5°	1408	133
15°	1322	372
25°	1150	516
35°	441	310
45°	219	170
55°	134	120
65°	79	78
75°	39	42
85°	12	12
90°	0	



TEST NUMBER: P584053

CATALOG NUMBER: HC820D010-HM80520930-81NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1416.9
2.5°	1414.3
5°	1407.6
7.5°	1391.9
10°	1368.4
12.5°	1346.1
15°	1322.5
17.5°	1292.4
20°	1255.8
22.5°	1211.2
25°	1149.7
27.5°	1052.8
30°	906.1
32.5°	663.9
35°	441.2
37.5°	326.0
40°	276.4
42.5°	244.9
45°	218.7
47.5°	193.8
50°	171.5
52.5°	150.6
55°	133.6
57.5°	117.8
60°	103.4
62.5°	90.3
65°	78.6
67.5°	66.8
70°	57.6
72.5°	47.2
75°	39.2
77.5°	31.4
80°	23.5
82.5°	17.0
85°	11.8
87.5°	5.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)