

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584550

Luminaire Tested: **HC840D010-HM82555835-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584550  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC840D010-HM82555835-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4797.1 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584550

CATALOG NUMBER: HC840D010-HM82555835-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584550

CATALOG NUMBER: HC840D010-HM82555835-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89882
5°	89129
10°	87955
15°	88960
20°	96067
25°	105056
30°	103786
35°	86088
40°	50672
45°	33104
50°	25661
55°	17048
60°	8295
65°	2568
70°	866
75°	763
80°	568
85°	1132



TEST NUMBER: P584550

CATALOG NUMBER: HC840D010-HM82555835-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	272.7	5.7
10°-20°	800.6	16.7
20°-30°	1399.7	29.2
30°-40°	1361.6	28.4
40°-50°	619.2	12.9
50°-60°	287.1	6.0
60°-70°	48.1	1.0
70°-80°	5.9	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2473.0	51.6
0°-40°	3834.6	79.9
0°-60°	4740.9	98.8
0°-90°	4797.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4797.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2915	
5°	2879	273
15°	2787	801
25°	3088	1400
35°	2287	1362
45°	759	619
55°	317	287
65°	35	48
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P584550

CATALOG NUMBER: HC840D010-HM82555835-81WDBB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2914.8
2.5°	2908.4
5°	2879.4
7.5°	2847.4
10°	2809.0
12.5°	2780.2
15°	2786.6
17.5°	2837.9
20°	2927.5
22.5°	3030.1
25°	3087.7
27.5°	3055.7
30°	2914.8
32.5°	2668.1
35°	2286.9
37.5°	1761.7
40°	1258.8
42.5°	938.4
45°	759.1
47.5°	640.6
50°	534.9
52.5°	426.0
55°	317.1
57.5°	217.8
60°	134.5
62.5°	73.7
65°	35.2
67.5°	16.1
70°	9.6
72.5°	6.4
75°	6.4
77.5°	3.2
80°	3.2
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)