

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584542

Luminaire Tested: **HC840D010-HM82555835-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC840D010-HM82555835-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4729.8 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584542

CATALOG NUMBER: HC840D010-HM82555835-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584542

CATALOG NUMBER: HC840D010-HM82555835-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58			
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216307
5°	197113
10°	168418
15°	146873
20°	130907
25°	116121
30°	95073
35°	54599
40°	24229
45°	14099
50°	8141
55°	4645
60°	2566
65°	1634
70°	1163
75°	763
80°	568
85°	1132



TEST NUMBER: P584542

CATALOG NUMBER: HC840D010-HM82555835-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	576.4	12.2
10°-20°	1293.2	27.3
20°-30°	1548.0	32.7
30°-40°	936.5	19.8
40°-50°	262.4	5.5
50°-60°	81.5	1.7
60°-70°	23.3	0.5
70°-80°	6.3	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3417.6	72.3
0°-40°	4354.1	92.1
0°-60°	4698.1	99.3
0°-90°	4729.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4729.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7015	
5°	6368	576
15°	4601	1293
25°	3413	1548
35°	1450	936
45°	323	262
55°	86	81
65°	22	23
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P584542

CATALOG NUMBER: HC840D010-HM82555835-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7014.7
2.5°	6816.2
5°	6367.9
7.5°	5862.1
10°	5378.7
12.5°	4956.1
15°	4600.7
17.5°	4287.0
20°	3989.2
22.5°	3713.9
25°	3412.9
27.5°	3073.5
30°	2670.1
32.5°	2148.3
35°	1450.4
37.5°	902.9
40°	601.9
42.5°	432.2
45°	323.3
47.5°	236.9
50°	169.7
52.5°	118.4
55°	86.4
57.5°	57.6
60°	41.6
62.5°	28.8
65°	22.4
67.5°	16.1
70°	12.9
72.5°	6.4
75°	6.4
77.5°	3.2
80°	3.2
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)