

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584127

Luminaire Tested: **HC825D010-HM82555830-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584127  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC825D010-HM82555830-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2565.5 lumens  
Efficiency: N/A  
Efficacy: 95.7 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584127

CATALOG NUMBER: HC825D010-HM82555830-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P584127

CATALOG NUMBER: HC825D010-HM82555830-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68		
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62		
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57		
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58734
5°	57411
10°	55651
15°	54523
20°	54034
25°	53227
30°	50419
35°	41890
40°	24672
45°	16319
50°	12842
55°	9451
60°	6568
65°	3998
70°	1749
75°	763
80°	568
85°	0



TEST NUMBER: P584127

CATALOG NUMBER: HC825D010-HM82555830-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	6.8
10°-20°	482.9	18.8
20°-30°	715.4	27.9
30°-40°	661.0	25.8
40°-50°	304.8	11.9
50°-60°	160.3	6.2
60°-70°	56.7	2.2
70°-80°	8.9	0.3
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1372.9	53.5
0°-40°	2033.9	79.3
0°-60°	2499.1	97.4
0°-90°	2565.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2565.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1905	
5°	1855	175
15°	1708	483
25°	1564	715
35°	1113	661
45°	374	305
55°	176	160
65°	55	57
75°	6	9
85°	0	1
90°	0	



TEST NUMBER: P584127

CATALOG NUMBER: HC825D010-HM82555830-81WDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1904.7
2.5°	1888.6
5°	1854.7
7.5°	1817.6
10°	1777.3
12.5°	1738.6
15°	1707.9
17.5°	1680.5
20°	1646.6
22.5°	1609.6
25°	1564.4
27.5°	1503.1
30°	1416.0
32.5°	1291.8
35°	1112.8
37.5°	854.8
40°	612.9
42.5°	459.7
45°	374.2
47.5°	317.7
50°	267.7
52.5°	219.4
55°	175.8
57.5°	138.7
60°	106.5
62.5°	80.7
65°	54.8
67.5°	32.2
70°	19.4
72.5°	11.3
75°	6.4
77.5°	4.8
80°	3.2
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)