

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584584

Luminaire Tested: **HC840D010-HM82555927-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC840D010-HM82555927-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3736.7 lumens
Efficiency: N/A
Efficacy: 91.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584584

CATALOG NUMBER: HC840D010-HM82555927-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584584

CATALOG NUMBER: HC840D010-HM82555927-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70011
5°	69427
10°	68514
15°	69294
20°	74832
25°	81831
30°	80841
35°	67059
40°	39473
45°	25786
50°	19985
55°	13279
60°	6463
65°	2007
70°	676
75°	596
80°	444
85°	885



TEST NUMBER: P584584

CATALOG NUMBER: HC840D010-HM82555927-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.4	5.7
10°-20°	623.6	16.7
20°-30°	1090.3	29.2
30°-40°	1060.6	28.4
40°-50°	482.3	12.9
50°-60°	223.6	6.0
60°-70°	37.5	1.0
70°-80°	4.6	0.1
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1926.3	51.6
0°-40°	2986.9	79.9
0°-60°	3692.8	98.8
0°-90°	3736.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3736.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2270	
5°	2243	212
15°	2171	624
25°	2405	1090
35°	1781	1061
45°	591	482
55°	247	224
65°	28	38
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P584584

CATALOG NUMBER: HC840D010-HM82555927-81WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2270.4
2.5°	2265.4
5°	2242.9
7.5°	2218.0
10°	2188.1
12.5°	2165.6
15°	2170.6
17.5°	2210.5
20°	2280.4
22.5°	2360.2
25°	2405.1
27.5°	2380.1
30°	2270.4
32.5°	2078.3
35°	1781.4
37.5°	1372.2
40°	980.6
42.5°	731.0
45°	591.3
47.5°	499.0
50°	416.6
52.5°	331.8
55°	247.0
57.5°	169.7
60°	104.8
62.5°	57.4
65°	27.5
67.5°	12.5
70°	7.5
72.5°	5.0
75°	5.0
77.5°	2.5
80°	2.5
82.5°	2.5
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)