

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584601

Luminaire Tested: **HC840D010-HM82555930-81WDBB**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584601  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC840D010-HM82555930-81WDBB  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4449.6 lumens  
Efficiency: N/A  
Efficacy: 108.5 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584601

CATALOG NUMBER: HC840D010-HM82555930-81WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P584601

CATALOG NUMBER: HC840D010-HM82555930-81WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	83369
5°	82678
10°	81583
15°	82517
20°	89110
25°	97445
30°	96266
35°	79855
40°	47001
45°	30705
50°	23799
55°	15817
60°	7697
65°	2386
70°	802
75°	703
80°	533
85°	1061



TEST NUMBER: P584601

CATALOG NUMBER: HC840D010-HM82555930-81WDBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.9	5.7
10°-20°	742.6	16.7
20°-30°	1298.3	29.2
30°-40°	1262.9	28.4
40°-50°	574.3	12.9
50°-60°	266.3	6.0
60°-70°	44.6	1.0
70°-80°	5.5	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2293.8	51.6
0°-40°	3556.8	79.9
0°-60°	4397.5	98.8
0°-90°	4449.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4449.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2704	
5°	2671	253
15°	2585	743
25°	2864	1298
35°	2121	1263
45°	704	574
55°	294	266
65°	33	45
75°	6	5
85°	3	2
90°	0	



TEST NUMBER: P584601

CATALOG NUMBER: HC840D010-HM82555930-81WDBB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2703.6
2.5°	2697.6
5°	2671.0
7.5°	2641.2
10°	2605.5
12.5°	2578.8
15°	2584.8
17.5°	2632.3
20°	2715.5
22.5°	2810.5
25°	2864.0
27.5°	2834.3
30°	2703.6
32.5°	2474.8
35°	2121.3
37.5°	1634.0
40°	1167.6
42.5°	870.5
45°	704.1
47.5°	594.2
50°	496.1
52.5°	395.2
55°	294.2
57.5°	202.1
60°	124.8
62.5°	68.3
65°	32.7
67.5°	14.9
70°	8.9
72.5°	5.9
75°	5.9
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)