

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584612

Luminaire Tested: **HC840D010-HM82555935-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC840D010-HM82555935-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4434.8 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584612

CATALOG NUMBER: HC840D010-HM82555935-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584612

CATALOG NUMBER: HC840D010-HM82555935-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	834702
5°	535395
10°	241860
15°	145928
20°	111205
25°	89803
30°	65808
35°	23829
40°	8896
45°	4038
50°	1290
55°	317
60°	185
65°	219
70°	0
75°	0
80°	533
85°	1061



TEST NUMBER: P584612

CATALOG NUMBER: HC840D010-HM82555935-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1319.2	29.7
10°-20°	1339.9	30.2
20°-30°	1199.5	27.0
30°-40°	483.2	10.9
40°-50°	79.3	1.8
50°-60°	7.2	0.2
60°-70°	2.6	0.1
70°-80°	2.0	0.0
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3858.5	87.0
0°-40°	4341.7	97.9
0°-60°	4428.1	99.8
0°-90°	4435.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4434.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27069	
5°	17296	###
15°	4571	1340
25°	2639	1199
35°	633	483
45°	93	79
55°	6	7
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584612

CATALOG NUMBER: HC840D010-HM82555935-81NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	27068.8
0.5°	26985.2
1°	26635.9
1.5°	26074.6
2°	25223.6
2.5°	24217.3
3°	22957.4
3.5°	21575.1
4°	20207.5
4.5°	18675.9
5°	17296.4
5.5°	15794.6
6°	14576.4
6.5°	13307.4
7°	12310.2
7.5°	11256.2
8°	10408.3
8.5°	9557.4
9°	8918.5
9.5°	8213.7
10°	7724.2
12.5°	5696.8
15°	4571.1
17.5°	3905.3
20°	3388.8
22.5°	2976.8
25°	2639.4
27.5°	2302.1
30°	1848.2
32.5°	1188.3
35°	633.0
37.5°	349.4
40°	221.0
42.5°	146.3
45°	92.6
47.5°	56.8
50°	26.9
52.5°	8.9
55°	5.9
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0



TEST NUMBER: P584612

CATALOG NUMBER: HC840D010-HM82555935-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	3.0
87.5°	3.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.0
70°		0.0



(END OF REPORT)