

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584227

Luminaire Tested: **HC825D010-HM82555940-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555940-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2639.3 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584227

CATALOG NUMBER: HC825D010-HM82555940-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584227

CATALOG NUMBER: HC825D010-HM82555940-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49452
5°	49041
10°	48396
15°	48946
20°	52859
25°	57800
30°	57102
35°	47368
40°	27880
45°	18211
50°	14123
55°	9381
60°	4564
65°	1416
70°	469
75°	417
80°	302
85°	601



TEST NUMBER: P584227

CATALOG NUMBER: HC825D010-HM82555940-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	5.7
10°-20°	440.5	16.7
20°-30°	770.1	29.2
30°-40°	749.2	28.4
40°-50°	340.7	12.9
50°-60°	158.0	6.0
60°-70°	26.5	1.0
70°-80°	3.2	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1360.7	51.6
0°-40°	2109.8	79.9
0°-60°	2608.5	98.8
0°-90°	2639.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2639.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1604	
5°	1584	150
15°	1533	440
25°	1699	770
35°	1258	749
45°	418	341
55°	174	158
65°	19	26
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P584227

CATALOG NUMBER: HC825D010-HM82555940-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1603.7
2.5°	1600.2
5°	1584.3
7.5°	1566.7
10°	1545.6
12.5°	1529.7
15°	1533.2
17.5°	1561.5
20°	1610.8
22.5°	1667.2
25°	1698.8
27.5°	1681.3
30°	1603.7
32.5°	1468.0
35°	1258.3
37.5°	969.3
40°	692.6
42.5°	516.4
45°	417.6
47.5°	352.5
50°	294.4
52.5°	234.4
55°	174.5
57.5°	119.8
60°	74.0
62.5°	40.6
65°	19.4
67.5°	8.8
70°	5.2
72.5°	3.5
75°	3.5
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)