

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593642

Luminaire Tested: **HC825D010-HM82555950-81WDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555950-81WDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2959.9 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593642

CATALOG NUMBER: HC825D010-HM82555950-81WDC

Luminous Intensity Polar Plot





TEST NUMBER: P593642

CATALOG NUMBER: HC825D010-HM82555950-81WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92																											
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84																											
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77																											
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70																											
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64																											
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59																											
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54																											
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50																											
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46																											
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71019
5°	69108
10°	68583
15°	67558
20°	65516
25°	63074
30°	58915
35°	48753
40°	29434
45°	19825
50°	14286
55°	8145
60°	3583
65°	1291
70°	469
75°	203
80°	0
85°	0



TEST NUMBER: P593642

CATALOG NUMBER: HC825D010-HM82555950-81WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.1	7.2
10°-20°	594.7	20.1
20°-30°	848.4	28.7
30°-40°	772.6	26.1
40°-50°	364.4	12.3
50°-60°	143.3	4.8
60°-70°	22.8	0.8
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1655.3	55.9
0°-40°	2427.8	82.0
0°-60°	2935.5	99.2
0°-90°	2959.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2959.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2303	
5°	2233	212
15°	2116	595
25°	1854	848
35°	1295	773
45°	455	364
55°	152	143
65°	18	23
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P593642

CATALOG NUMBER: HC825D010-HM82555950-81WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2303.1
2.5°	2273.1
5°	2232.6
7.5°	2209.7
10°	2190.3
12.5°	2158.6
15°	2116.2
17.5°	2063.4
20°	1996.5
22.5°	1926.0
25°	1853.8
27.5°	1765.6
30°	1654.6
32.5°	1504.8
35°	1295.1
37.5°	1000.9
40°	731.2
42.5°	562.1
45°	454.6
47.5°	373.5
50°	297.8
52.5°	223.7
55°	151.5
57.5°	95.1
60°	58.1
62.5°	35.2
65°	17.7
67.5°	8.8
70°	5.2
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)