

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593741

Luminaire Tested: **HC840D010-HM82555950-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593741  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC840D010-HM82555950-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5251.8 lumens  
Efficiency: N/A  
Efficacy: 128.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 41  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593741

CATALOG NUMBER: HC840D010-HM82555950-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P593741

CATALOG NUMBER: HC840D010-HM82555950-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92				92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68				68
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62				62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57				57
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	120237
5°	117527
10°	113923
15°	111616
20°	110617
25°	108962
30°	103213
35°	85753
40°	50503
45°	33405
50°	26294
55°	19349
60°	13438
65°	8187
70°	3570
75°	1573
80°	1154
85°	0



TEST NUMBER: P593741

CATALOG NUMBER: HC840D010-HM82555950-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	357.5	6.8
10°-20°	988.5	18.8
20°-30°	1464.5	27.9
30°-40°	1353.2	25.8
40°-50°	624.0	11.9
50°-60°	328.2	6.2
60°-70°	116.0	2.2
70°-80°	18.2	0.3
80°-90°	1.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2810.5	53.5
0°-40°	4163.7	79.3
0°-60°	5115.9	97.4
0°-90°	5251.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5251.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3899	
5°	3797	358
15°	3496	988
25°	3202	1464
35°	2278	1353
45°	766	624
55°	360	328
65°	112	116
75°	13	18
85°	0	2
90°	0	



TEST NUMBER: P593741

CATALOG NUMBER: HC840D010-HM82555950-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3899.2
2.5°	3866.1
5°	3796.8
7.5°	3720.9
10°	3638.3
12.5°	3559.1
15°	3496.3
17.5°	3440.2
20°	3370.9
22.5°	3295.0
25°	3202.5
27.5°	3077.1
30°	2898.7
32.5°	2644.5
35°	2278.0
37.5°	1749.8
40°	1254.6
42.5°	940.9
45°	766.0
47.5°	650.5
50°	548.1
52.5°	449.0
55°	359.9
57.5°	283.9
60°	217.9
62.5°	165.1
65°	112.2
67.5°	66.0
70°	39.6
72.5°	23.1
75°	13.2
77.5°	9.9
80°	6.5
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)