

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584262

Luminaire Tested: **HC830D010-HM82555830-81WDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584262  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC830D010-HM82555830-81WDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3644.9 lumens  
Efficiency: N/A  
Efficacy: 130.2 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584262

CATALOG NUMBER: HC830D010-HM82555830-81WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584262

CATALOG NUMBER: HC830D010-HM82555830-81WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	79	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	71	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46	46	46	46
10	66	55	49	45	65	55	49	45	54	48	44	53	48	44	52	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	87452
5°	85099
10°	84452
15°	83191
20°	80673
25°	77663
30°	72549
35°	60035
40°	36245
45°	24412
50°	17592
55°	10032
60°	4416
65°	1576
70°	586
75°	250
80°	0
85°	0



TEST NUMBER: P584262

CATALOG NUMBER: HC830D010-HM82555830-81WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	261.2	7.2
10°-20°	732.4	20.1
20°-30°	1044.7	28.7
30°-40°	951.3	26.1
40°-50°	448.8	12.3
50°-60°	176.5	4.8
60°-70°	28.1	0.8
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2038.3	55.9
0°-40°	2989.6	82.0
0°-60°	3614.9	99.2
0°-90°	3644.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3644.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2836	
5°	2749	261
15°	2606	732
25°	2283	1045
35°	1595	951
45°	560	449
55°	187	176
65°	22	28
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P584262

CATALOG NUMBER: HC830D010-HM82555830-81WDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2836.0
2.5°	2799.1
5°	2749.2
7.5°	2721.0
10°	2697.1
12.5°	2658.0
15°	2605.9
17.5°	2540.9
20°	2458.4
22.5°	2371.6
25°	2282.6
27.5°	2174.2
30°	2037.5
32.5°	1853.1
35°	1594.8
37.5°	1232.5
40°	900.4
42.5°	692.2
45°	559.8
47.5°	460.0
50°	366.7
52.5°	275.6
55°	186.6
57.5°	117.1
60°	71.6
62.5°	43.4
65°	21.6
67.5°	10.8
70°	6.5
72.5°	2.1
75°	2.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)