

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584661

Luminaire Tested: **HC845D010-HM82555830-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584661
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555830-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4749.9 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584661

CATALOG NUMBER: HC845D010-HM82555830-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P584661

CATALOG NUMBER: HC845D010-HM82555830-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	56	64	60	56	63	59	56	55
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217226
5°	197951
10°	169129
15°	147496
20°	131458
25°	116614
30°	95479
35°	54829
40°	24329
45°	14160
50°	8175
55°	4666
60°	2578
65°	1642
70°	1163
75°	774
80°	568
85°	1132



TEST NUMBER: P584661

CATALOG NUMBER: HC845D010-HM82555830-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	578.9	12.2
10°-20°	1298.7	27.3
20°-30°	1554.5	32.7
30°-40°	940.5	19.8
40°-50°	263.5	5.5
50°-60°	81.8	1.7
60°-70°	23.4	0.5
70°-80°	6.4	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3432.1	72.3
0°-40°	4372.6	92.1
0°-60°	4717.9	99.3
0°-90°	4749.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4749.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7044	
5°	6395	579
15°	4620	1299
25°	3427	1555
35°	1456	940
45°	325	264
55°	87	82
65°	22	23
75°	6	6
85°	3	2
90°	0	



TEST NUMBER: P584661

CATALOG NUMBER: HC845D010-HM82555830-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	7044.5
2.5°	6845.0
5°	6395.0
7.5°	5886.9
10°	5401.4
12.5°	4977.0
15°	4620.2
17.5°	4305.1
20°	4006.0
22.5°	3729.6
25°	3427.4
27.5°	3086.5
30°	2681.5
32.5°	2157.4
35°	1456.5
37.5°	906.7
40°	604.4
42.5°	434.0
45°	324.7
47.5°	237.9
50°	170.4
52.5°	118.9
55°	86.8
57.5°	57.8
60°	41.8
62.5°	29.0
65°	22.5
67.5°	16.1
70°	12.9
72.5°	6.5
75°	6.5
77.5°	3.2
80°	3.2
82.5°	3.2
85°	3.2
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)