

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584663

Luminaire Tested: **HC845D010-HM82555830-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555830-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4775.5 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584663

CATALOG NUMBER: HC845D010-HM82555830-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584663

CATALOG NUMBER: HC845D010-HM82555830-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	898860
5°	576548
10°	260450
15°	157146
20°	119753
25°	96707
30°	70864
35°	25658
40°	9576
45°	4348
50°	1391
55°	349
60°	197
65°	233
70°	0
75°	0
80°	568
85°	1132



TEST NUMBER: P584663

CATALOG NUMBER: HC845D010-HM82555830-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1420.6	29.7
10°-20°	1442.9	30.2
20°-30°	1291.6	27.0
30°-40°	520.3	10.9
40°-50°	85.3	1.8
50°-60°	7.8	0.2
60°-70°	2.8	0.1
70°-80°	2.1	0.0
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4155.1	87.0
0°-40°	4675.4	97.9
0°-60°	4768.4	99.9
0°-90°	4776.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4775.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	29149	
5°	18626	###
15°	4922	1443
25°	2842	1292
35°	682	520
45°	100	85
55°	6	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584663

CATALOG NUMBER: HC845D010-HM82555830-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	29149.4
0.5°	29059.4
1°	28683.1
1.5°	28078.7
2°	27162.3
2.5°	26078.8
3°	24722.0
3.5°	23233.4
4°	21760.8
4.5°	20111.3
5°	18625.9
5.5°	17008.6
6°	15696.9
6.5°	14330.3
7°	13256.4
7.5°	12121.4
8°	11208.4
8.5°	10292.0
9°	9603.9
9.5°	8845.1
10°	8317.9
12.5°	6134.7
15°	4922.5
17.5°	4205.6
20°	3649.3
22.5°	3205.6
25°	2842.3
27.5°	2478.9
30°	1990.2
32.5°	1279.6
35°	681.6
37.5°	376.2
40°	237.9
42.5°	157.5
45°	99.7
47.5°	61.1
50°	29.0
52.5°	9.6
55°	6.5
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2



TEST NUMBER: P584663

CATALOG NUMBER: HC845D010-HM82555830-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.2
80°	3.2
82.5°	3.2
85°	3.2
87.5°	3.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.2
70°		0.0



(END OF REPORT)