

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584666

Luminaire Tested: **HC845D010-HM82555830-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555830-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4782.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584666

CATALOG NUMBER: HC845D010-HM82555830-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P584666

CATALOG NUMBER: HC845D010-HM82555830-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112250
5°	110788
10°	106730
15°	102556
20°	99719
25°	96717
30°	86791
35°	56895
40°	31458
45°	26222
50°	23910
55°	22822
60°	21215
65°	19241
70°	17401
75°	15703
80°	14277
85°	13657



TEST NUMBER: P584666

CATALOG NUMBER: HC845D010-HM82555830-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.3	7.0
10°-20°	906.3	19.0
20°-30°	1289.9	27.0
30°-40°	954.6	20.0
40°-50°	472.8	9.9
50°-60°	377.4	7.9
60°-70°	262.0	5.5
70°-80°	141.2	3.0
80°-90°	41.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2532.5	53.0
0°-40°	3487.1	72.9
0°-60°	4337.3	90.7
0°-90°	4782.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4782.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3640	
5°	3579	336
15°	3212	906
25°	2843	1290
35°	1511	955
45°	601	473
55°	424	377
65°	264	262
75°	132	141
85°	39	42
90°	0	



TEST NUMBER: P584666

CATALOG NUMBER: HC845D010-HM82555830-81PSMDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3640.2
2.5°	3624.1
5°	3579.1
7.5°	3508.3
10°	3408.6
12.5°	3305.7
15°	3212.5
17.5°	3122.4
20°	3038.8
22.5°	2955.3
25°	2842.6
27.5°	2678.7
30°	2437.5
32.5°	2067.6
35°	1511.4
37.5°	1032.2
40°	781.5
42.5°	668.8
45°	601.3
47.5°	546.6
50°	498.4
52.5°	456.6
55°	424.5
57.5°	385.9
60°	344.0
62.5°	302.3
65°	263.7
67.5°	225.1
70°	193.0
72.5°	160.8
75°	131.8
77.5°	106.2
80°	80.4
82.5°	57.8
85°	38.6
87.5°	16.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)