

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584329

Luminaire Tested: **HC830D010-HM82555930-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555930-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3195.6 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584329

CATALOG NUMBER: HC830D010-HM82555930-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P584329

CATALOG NUMBER: HC830D010-HM82555930-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59872
5°	59376
10°	58591
15°	59264
20°	63996
25°	69984
30°	69134
35°	57351
40°	33757
45°	22053
50°	17093
55°	11360
60°	5532
65°	1707
70°	577
75°	512
80°	373
85°	743



TEST NUMBER: P584329

CATALOG NUMBER: HC830D010-HM82555930-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.7	5.7
10°-20°	533.3	16.7
20°-30°	932.4	29.2
30°-40°	907.0	28.4
40°-50°	412.5	12.9
50°-60°	191.3	6.0
60°-70°	32.1	1.0
70°-80°	3.9	0.1
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1647.4	51.6
0°-40°	2554.4	79.9
0°-60°	3158.2	98.8
0°-90°	3195.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3195.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1942	
5°	1918	182
15°	1856	533
25°	2057	932
35°	1524	907
45°	506	412
55°	211	191
65°	23	32
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P584329

CATALOG NUMBER: HC830D010-HM82555930-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1941.6
2.5°	1937.4
5°	1918.2
7.5°	1896.9
10°	1871.2
12.5°	1852.1
15°	1856.4
17.5°	1890.5
20°	1950.2
22.5°	2018.4
25°	2056.9
27.5°	2035.6
30°	1941.6
32.5°	1777.4
35°	1523.5
37.5°	1173.5
40°	838.6
42.5°	625.2
45°	505.7
47.5°	426.7
50°	356.3
52.5°	283.8
55°	211.3
57.5°	145.1
60°	89.7
62.5°	49.1
65°	23.4
67.5°	10.7
70°	6.4
72.5°	4.3
75°	4.3
77.5°	2.1
80°	2.1
82.5°	2.1
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)