

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584337

Luminaire Tested: **HC830D010-HM82555935-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555935-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3465.9 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584337

CATALOG NUMBER: HC830D010-HM82555935-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P584337

CATALOG NUMBER: HC830D010-HM82555935-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58	58	58	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207084
5°	197583
10°	170588
15°	130442
20°	99808
25°	78960
30°	59648
35°	31730
40°	12084
45°	5796
50°	2471
55°	1038
60°	395
65°	314
70°	189
75°	0
80°	0
85°	0



TEST NUMBER: P584337

CATALOG NUMBER: HC830D010-HM82555935-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	579.4	16.7
10°-20°	1140.7	32.9
20°-30°	1062.4	30.7
30°-40°	548.1	15.8
40°-50°	111.7	3.2
50°-60°	19.1	0.6
60°-70°	3.7	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2782.5	80.3
0°-40°	3330.6	96.1
0°-60°	3461.4	99.9
0°-90°	3465.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3465.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6716	
5°	6383	579
15°	4086	1141
25°	2321	1062
35°	843	548
45°	133	112
55°	19	19
65°	4	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584337

CATALOG NUMBER: HC830D010-HM82555935-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	6715.6
2.5°	6625.5
5°	6383.1
7.5°	5984.1
10°	5448.0
12.5°	4744.5
15°	4086.0
17.5°	3515.4
20°	3041.5
22.5°	2655.4
25°	2320.7
27.5°	2003.3
30°	1675.2
32.5°	1284.7
35°	842.9
37.5°	489.0
40°	300.2
42.5°	197.4
45°	132.9
47.5°	83.7
50°	51.5
52.5°	30.1
55°	19.3
57.5°	8.6
60°	6.4
62.5°	4.3
65°	4.3
67.5°	2.1
70°	2.1
72.5°	2.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)