

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593760

Luminaire Tested: **HC845D010-HM82555850-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555850-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5482.4 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593760

CATALOG NUMBER: HC845D010-HM82555850-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P593760

CATALOG NUMBER: HC845D010-HM82555850-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96			96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87			87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83			83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80			80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76			76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68			68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66			66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1031943
5°	661913
10°	299011
15°	180416
20°	137483
25°	111024
30°	81358
35°	29457
40°	10997
45°	4993
50°	1593
55°	398
60°	222
65°	263
70°	0
75°	0
80°	639
85°	1274



TEST NUMBER: P593760

CATALOG NUMBER: HC845D010-HM82555850-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1630.9	29.7
10°-20°	1656.5	30.2
20°-30°	1482.9	27.0
30°-40°	597.3	10.9
40°-50°	98.0	1.8
50°-60°	8.9	0.2
60°-70°	3.1	0.1
70°-80°	2.4	0.0
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4770.3	87.0
0°-40°	5367.6	97.9
0°-60°	5474.4	99.9
0°-90°	5483.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5482.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	33465	
5°	21384	###
15°	5651	1657
25°	3263	1483
35°	782	597
45°	114	98
55°	7	9
65°	4	3
75°	0	2
85°	4	3
90°	0	



TEST NUMBER: P593760

CATALOG NUMBER: HC845D010-HM82555850-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	33465.2
0.5°	33361.9
1°	32930.0
1.5°	32236.0
2°	31184.0
2.5°	29940.0
3°	28382.3
3.5°	26673.2
4°	24982.7
4.5°	23089.0
5°	21383.7
5.5°	19526.9
6°	18020.9
6.5°	16452.0
7°	15219.2
7.5°	13916.1
8°	12867.8
8.5°	11815.9
9°	11025.8
9.5°	10154.8
10°	9549.4
12.5°	7042.9
15°	5651.4
17.5°	4828.2
20°	4189.6
22.5°	3680.2
25°	3263.1
27.5°	2845.9
30°	2284.9
32.5°	1469.2
35°	782.5
37.5°	431.9
40°	273.2
42.5°	180.9
45°	114.5
47.5°	70.1
50°	33.2
52.5°	11.0
55°	7.4
57.5°	3.6
60°	3.6
62.5°	3.6
65°	3.6



TEST NUMBER: P593760

CATALOG NUMBER: HC845D010-HM82555850-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.6
80°	3.6
82.5°	3.6
85°	3.6
87.5°	3.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.6
70°		0.0



(END OF REPORT)