

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593669

Luminaire Tested: **HC830D010-HM82555950-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC830D010-HM82555950-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3551.3 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593669

CATALOG NUMBER: HC830D010-HM82555950-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P593669

CATALOG NUMBER: HC830D010-HM82555950-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66539
5°	65988
10°	65116
15°	65856
20°	71121
25°	77776
30°	76832
35°	63732
40°	37513
45°	24504
50°	18992
55°	12618
60°	6143
65°	1897
70°	640
75°	572
80°	426
85°	849



TEST NUMBER: P593669

CATALOG NUMBER: HC830D010-HM82555950-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	201.9	5.7
10°-20°	592.7	16.7
20°-30°	1036.2	29.2
30°-40°	1008.0	28.4
40°-50°	458.4	12.9
50°-60°	212.5	6.0
60°-70°	35.6	1.0
70°-80°	4.4	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1830.8	51.6
0°-40°	2838.8	79.9
0°-60°	3509.7	98.8
0°-90°	3551.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3551.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2158	
5°	2132	202
15°	2063	593
25°	2286	1036
35°	1693	1008
45°	562	458
55°	235	213
65°	26	36
75°	5	4
85°	2	2
90°	0	



TEST NUMBER: P593669

CATALOG NUMBER: HC830D010-HM82555950-81WDBB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2157.8
2.5°	2153.0
5°	2131.8
7.5°	2108.0
10°	2079.6
12.5°	2058.3
15°	2062.9
17.5°	2100.8
20°	2167.3
22.5°	2243.2
25°	2285.9
27.5°	2262.2
30°	2157.8
32.5°	1975.2
35°	1693.0
37.5°	1304.2
40°	931.9
42.5°	694.7
45°	561.9
47.5°	474.3
50°	395.9
52.5°	315.3
55°	234.7
57.5°	161.2
60°	99.6
62.5°	54.6
65°	26.0
67.5°	11.9
70°	7.1
72.5°	4.8
75°	4.8
77.5°	2.4
80°	2.4
82.5°	2.4
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)