

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584715

Luminaire Tested: **HC845D010-HM82555927-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584715
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555927-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3595.4 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584715

CATALOG NUMBER: HC845D010-HM82555927-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P584715

CATALOG NUMBER: HC845D010-HM82555927-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	70	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286078
5°	242368
10°	175848
15°	132057
20°	104195
25°	84046
30°	62283
35°	25233
40°	10643
45°	5708
50°	2562
55°	1290
60°	826
65°	584
70°	487
75°	322
80°	479
85°	955



TEST NUMBER: P584715

CATALOG NUMBER: HC845D010-HM82555927-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	672.3	18.7
10°-20°	1161.8	32.3
20°-30°	1123.3	31.2
30°-40°	493.4	13.7
40°-50°	106.7	3.0
50°-60°	23.9	0.7
60°-70°	8.3	0.2
70°-80°	3.2	0.1
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2957.4	82.3
0°-40°	3450.8	96.0
0°-60°	3581.4	99.6
0°-90°	3595.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3595.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9277	
5°	7830	672
15°	4137	1162
25°	2470	1123
35°	670	493
45°	131	107
55°	24	24
65°	8	8
75°	3	3
85°	3	3
90°	0	



TEST NUMBER: P584715

CATALOG NUMBER: HC845D010-HM82555927-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9277.3
1°	9207.8
2°	9018.3
3°	8676.4
4°	8267.8
5°	7829.9
6°	7351.8
7°	6871.2
8°	6419.8
9°	6000.6
10°	5616.0
11°	5252.8
12°	4927.1
13°	4630.7
14°	4369.0
15°	4136.6
17.5°	3615.8
20°	3175.2
22.5°	2788.0
25°	2470.2
27.5°	2147.1
30°	1749.2
32.5°	1188.4
35°	670.3
37.5°	395.2
40°	264.4
42.5°	187.0
45°	130.9
47.5°	85.5
50°	53.4
52.5°	32.0
55°	24.0
57.5°	18.7
60°	13.4
62.5°	10.7
65°	8.0
67.5°	5.4
70°	5.4
72.5°	2.7
75°	2.7
77.5°	2.7
80°	2.7
82.5°	2.7



TEST NUMBER: P584715

CATALOG NUMBER: HC845D010-HM82555927-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°	2.7
87.5°	2.7



(END OF REPORT)