

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584731

Luminaire Tested: **HC845D010-HM82555930-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555930-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4695.6 lumens
Efficiency: N/A
Efficacy: 106.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584731

CATALOG NUMBER: HC845D010-HM82555930-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584731

CATALOG NUMBER: HC845D010-HM82555930-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	883787
5°	566881
10°	256082
15°	154513
20°	117745
25°	95084
30°	69679
35°	25233
40°	9415
45°	4269
50°	1367
55°	339
60°	197
65°	233
70°	0
75°	0
80°	568
85°	1132



TEST NUMBER: P584731

CATALOG NUMBER: HC845D010-HM82555930-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1396.7	29.7
10°-20°	1418.7	30.2
20°-30°	1270.0	27.0
30°-40°	511.6	10.9
40°-50°	83.9	1.8
50°-60°	7.6	0.2
60°-70°	2.8	0.1
70°-80°	2.1	0.0
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4085.4	87.0
0°-40°	4597.0	97.9
0°-60°	4688.5	99.8
0°-90°	4696.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4695.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28661	
5°	18314	###
15°	4840	1419
25°	2795	1270
35°	670	512
45°	98	84
55°	6	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584731

CATALOG NUMBER: HC845D010-HM82555930-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	28660.6
0.5°	28572.1
1°	28202.2
1.5°	27607.8
2°	26706.9
2.5°	25641.5
3°	24307.4
3.5°	22843.7
4°	21395.9
4.5°	19774.1
5°	18313.6
5.5°	16723.5
6°	15433.6
6.5°	14090.1
7°	13034.1
7.5°	11918.1
8°	11020.3
8.5°	10119.4
9°	9442.9
9.5°	8696.9
10°	8178.4
12.5°	6031.8
15°	4840.0
17.5°	4135.1
20°	3588.1
22.5°	3151.9
25°	2794.6
27.5°	2437.4
30°	1956.9
32.5°	1258.2
35°	670.3
37.5°	369.8
40°	233.9
42.5°	155.0
45°	97.9
47.5°	60.1
50°	28.5
52.5°	9.5
55°	6.3
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2



TEST NUMBER: P584731

CATALOG NUMBER: HC845D010-HM82555930-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.2
80°	3.2
82.5°	3.2
85°	3.2
87.5°	3.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		3.2
70°		0.0



(END OF REPORT)