

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584371

Luminaire Tested: **HC835D010-HM82555827-81MDC**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584371  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC835D010-HM82555827-81MDC  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4314.9 lumens  
Efficiency: N/A  
Efficacy: 128.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct

Input Watts (W): 33.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584371  
CATALOG NUMBER: HC835D010-HM82555827-81MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P584371

CATALOG NUMBER: HC835D010-HM82555827-81MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84	84	84	84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79	79	79	79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64	64	64	64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61	61	61	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58	58	58	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	257810
5°	245983
10°	212374
15°	162392
20°	124252
25°	98302
30°	74258
35°	39504
40°	15047
45°	7222
50°	3075
55°	1296
60°	493
65°	394
70°	234
75°	0
80°	0
85°	0



TEST NUMBER: P584371

CATALOG NUMBER: HC835D010-HM82555827-81MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	721.4	16.7
10°-20°	1420.1	32.9
20°-30°	1322.6	30.7
30°-40°	682.4	15.8
40°-50°	139.0	3.2
50°-60°	23.8	0.6
60°-70°	4.6	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3464.0	80.3
0°-40°	4146.4	96.1
0°-60°	4309.3	99.9
0°-90°	4314.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4314.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8361	
5°	7947	721
15°	5087	1420
25°	2889	1323
35°	1049	682
45°	166	139
55°	24	24
65°	5	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P584371

CATALOG NUMBER: HC835D010-HM82555827-81MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8360.6
2.5°	8248.3
5°	7946.7
7.5°	7450.0
10°	6782.5
12.5°	5906.6
15°	5086.8
17.5°	4376.5
20°	3786.4
22.5°	3305.8
25°	2889.2
27.5°	2494.0
30°	2085.5
32.5°	1599.4
35°	1049.4
37.5°	608.8
40°	373.8
42.5°	245.7
45°	165.6
47.5°	104.1
50°	64.1
52.5°	37.4
55°	24.1
57.5°	10.7
60°	8.0
62.5°	5.4
65°	5.4
67.5°	2.6
70°	2.6
72.5°	2.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)