

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584751

Luminaire Tested: **HC845D010-HM82555935-81PSMDW**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P584751  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC845D010-HM82555935-81PSMDW  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4727.1 lumens  
Efficiency: N/A  
Efficacy: 107.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P584751

CATALOG NUMBER: HC845D010-HM82555935-81PSMDW

### Luminous Intensity Polar Plot





TEST NUMBER: P584751

CATALOG NUMBER: HC845D010-HM82555935-81PSMDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	110961
5°	109516
10°	105509
15°	101381
20°	98574
25°	95608
30°	85798
35°	56244
40°	31092
45°	25926
50°	23636
55°	22558
60°	20981
65°	19015
70°	17193
75°	15524
80°	14100
85°	13480



TEST NUMBER: P584751

CATALOG NUMBER: HC845D010-HM82555935-81PSMDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.4	7.0
10°-20°	895.9	19.0
20°-30°	1275.1	27.0
30°-40°	943.7	20.0
40°-50°	467.4	9.9
50°-60°	373.1	7.9
60°-70°	259.0	5.5
70°-80°	139.5	3.0
80°-90°	41.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2503.4	53.0
0°-40°	3447.1	72.9
0°-60°	4287.6	90.7
0°-90°	4727.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4727.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3598	
5°	3538	332
15°	3176	896
25°	2810	1275
35°	1494	944
45°	594	467
55°	420	373
65°	261	259
75°	130	140
85°	38	41
90°	0	



TEST NUMBER: P584751

CATALOG NUMBER: HC845D010-HM82555935-81PSMDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3598.4
2.5°	3582.5
5°	3538.0
7.5°	3468.1
10°	3369.6
12.5°	3267.7
15°	3175.7
17.5°	3086.6
20°	3003.9
22.5°	2921.4
25°	2810.0
27.5°	2647.9
30°	2409.6
32.5°	2044.0
35°	1494.1
37.5°	1020.4
40°	772.4
42.5°	661.2
45°	594.5
47.5°	540.4
50°	492.7
52.5°	451.4
55°	419.6
57.5°	381.5
60°	340.2
62.5°	298.8
65°	260.6
67.5°	222.5
70°	190.7
72.5°	158.9
75°	130.3
77.5°	104.9
80°	79.4
82.5°	57.2
85°	38.1
87.5°	15.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)