

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584757

Luminaire Tested: **HC845D010-HM82555935-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555935-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4882.9 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584757

CATALOG NUMBER: HC845D010-HM82555935-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584757

CATALOG NUMBER: HC845D010-HM82555935-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97622
5°	97502
10°	96538
15°	95380
20°	94498
25°	93437
30°	88162
35°	71791
40°	39662
45°	26475
50°	23483
55°	22042
60°	21758
65°	21568
70°	19492
75°	17419
80°	15254
85°	13480



TEST NUMBER: P584757

CATALOG NUMBER: HC845D010-HM82555935-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	298.5	6.1
10°-20°	843.6	17.3
20°-30°	1253.5	25.7
30°-40°	1128.9	23.1
40°-50°	500.4	10.2
50°-60°	370.7	7.6
60°-70°	288.2	5.9
70°-80°	156.3	3.2
80°-90°	42.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2395.7	49.1
0°-40°	3524.5	72.2
0°-60°	4395.6	90.0
0°-90°	4882.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4882.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3166	
5°	3150	299
15°	2988	844
25°	2746	1254
35°	1907	1129
45°	607	500
55°	410	371
65°	296	288
75°	146	156
85°	38	43
90°	0	



TEST NUMBER: P584757

CATALOG NUMBER: HC845D010-HM82555935-81WDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3165.8
2.5°	3159.4
5°	3149.9
7.5°	3124.4
10°	3083.1
12.5°	3035.5
15°	2987.7
17.5°	2940.1
20°	2879.7
22.5°	2819.3
25°	2746.2
27.5°	2634.9
30°	2476.0
32.5°	2247.2
35°	1907.1
37.5°	1423.9
40°	985.3
42.5°	727.8
45°	607.1
47.5°	537.1
50°	489.5
52.5°	445.0
55°	410.0
57.5°	381.5
60°	352.8
62.5°	327.4
65°	295.6
67.5°	257.5
70°	216.2
72.5°	181.2
75°	146.2
77.5°	114.4
80°	85.9
82.5°	60.4
85°	38.1
87.5°	15.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)