

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593780

Luminaire Tested: **HC845D010-HM82555950-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555950-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4705.2 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593780

CATALOG NUMBER: HC845D010-HM82555950-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593780

CATALOG NUMBER: HC845D010-HM82555950-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117277
5°	116966
10°	115015
15°	113337
20°	110617
25°	105005
30°	86613
35°	44593
40°	29856
45°	25599
50°	22091
55°	19279
60°	17120
65°	15388
70°	13948
75°	12570
80°	11223
85°	11216



TEST NUMBER: P593780

CATALOG NUMBER: HC845D010-HM82555950-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	357.3	7.6
10°-20°	998.8	21.2
20°-30°	1384.0	29.4
30°-40°	831.3	17.7
40°-50°	455.1	9.7
50°-60°	323.3	6.9
60°-70°	209.9	4.5
70°-80°	112.2	2.4
80°-90°	33.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2740.1	58.2
0°-40°	3571.3	75.9
0°-60°	4349.7	92.4
0°-90°	4705.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4705.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3803	
5°	3779	357
15°	3550	999
25°	3086	1384
35°	1185	831
45°	587	455
55°	359	323
65°	211	210
75°	106	112
85°	32	33
90°	0	



TEST NUMBER: P593780

CATALOG NUMBER: HC845D010-HM82555950-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3803.2
2.5°	3796.2
5°	3778.7
7.5°	3736.5
10°	3673.2
12.5°	3613.4
15°	3550.2
17.5°	3469.4
20°	3370.9
22.5°	3251.4
25°	3086.2
27.5°	2826.1
30°	2432.5
32.5°	1782.1
35°	1184.6
37.5°	875.3
40°	741.7
42.5°	657.3
45°	587.0
47.5°	520.2
50°	460.5
52.5°	404.2
55°	358.6
57.5°	316.4
60°	277.6
62.5°	242.6
65°	210.9
67.5°	179.2
70°	154.7
72.5°	126.6
75°	105.5
77.5°	84.3
80°	63.2
82.5°	45.7
85°	31.7
87.5°	14.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)