

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584400

Luminaire Tested: **HC835D010-HM82555830-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC835D010-HM82555830-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4004.9 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584400

CATALOG NUMBER: HC835D010-HM82555830-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584400

CATALOG NUMBER: HC835D010-HM82555830-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80066
5°	79970
10°	79179
15°	78230
20°	77507
25°	76636
30°	72310
35°	58883
40°	32533
45°	21713
50°	19256
55°	18080
60°	17842
65°	17694
70°	15985
75°	14285
80°	12502
85°	11074



TEST NUMBER: P584400

CATALOG NUMBER: HC835D010-HM82555830-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.9	6.1
10°-20°	691.9	17.3
20°-30°	1028.1	25.7
30°-40°	925.9	23.1
40°-50°	410.5	10.2
50°-60°	304.0	7.6
60°-70°	236.4	5.9
70°-80°	128.2	3.2
80°-90°	35.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1964.9	49.1
0°-40°	2890.8	72.2
0°-60°	3605.3	90.0
0°-90°	4004.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4004.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2596	
5°	2584	245
15°	2450	692
25°	2252	1028
35°	1564	926
45°	498	410
55°	336	304
65°	242	236
75°	120	128
85°	31	35
90°	0	



TEST NUMBER: P584400

CATALOG NUMBER: HC835D010-HM82555830-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2596.5
2.5°	2591.3
5°	2583.5
7.5°	2562.6
10°	2528.7
12.5°	2489.7
15°	2450.5
17.5°	2411.5
20°	2361.9
22.5°	2312.4
25°	2252.4
27.5°	2161.2
30°	2030.8
32.5°	1843.1
35°	1564.2
37.5°	1167.9
40°	808.2
42.5°	597.0
45°	497.9
47.5°	440.6
50°	401.4
52.5°	365.0
55°	336.3
57.5°	312.8
60°	289.3
62.5°	268.5
65°	242.5
67.5°	211.2
70°	177.3
72.5°	148.6
75°	119.9
77.5°	93.8
80°	70.4
82.5°	49.5
85°	31.3
87.5°	13.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)